




adorne Collection  
**adorne® 20A Tamper Resistant Receptacle Ultra Fast 30W Power Delivery USB White**  
Part No. ARTRUSB20PD30W4



Charge devices up to 2X faster with the Ultra-Fast PLUS Power Delivery USB Outlet. Made to deliver a leading 30 Watts of power and featuring two built-in Type-C USB connections, this solution adds the intelligent charging of advanced Power Delivery to the industry-leading amperage of our Ultra-Fast line. The result is a faster, future-proof option for convenient in-wall charging, specially designed to optimize performance for your Power Delivery-enabled devices. Also includes multi-layered overcurrent protection to keep the outlet and your devices safe from damage. Easily replace a traditional outlet in as little as ten minutes to gain modern functionality and the unique, contemporary aesthetic of adorne.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Charge the latest devices up to 2X as fast, thanks to the industry-leading 6.0A of our Ultra-Fast line and a whopping 30W of power courtesy of advanced Power Delivery

Built for intelligent charging, the outlet detects and delivers the precise amount of power needed to maximize charging speeds

Provides fast and convenient built-in charging through two future-proof USB Type-C ports, accommodating new and upcoming devices without an adapter

Helpful indicator light lets you see charging status at a glance. Light glows yellow while charging is in progress, and shows green once the device battery is sufficiently charged

Includes multiple layers of overcurrent protection, ensuring the outlet and your favorite devices can charge at optimal levels without risk of damage

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty

The adorne two module USB Outlet lets you plug directly into the wall and skip searching for clunky cable connectors

Replaces a traditional outlet easily, in as little as 10 minutes

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets

Compatible with the 1-Gang-Plus (1+ Gang) adorne Wall Plates only. Cannot be used in multi-gang installations

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007378115
Country Of Origin	China	Number of Receptacles	2
Application Sector	Residential/Commercial	Warranty Type	Limited Lifetime Warranty

---

Type	Tamper-Resistant, USB
------	-----------------------

---

#### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

#### Technical Information

---

Connection	USB Type C/C	Number of USBs	2
Output Current	6A	Current Rating	20 A
Indoor/Outdoor	Indoor	Voltage	125 VAC

---