



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

Features & Benefits

Meets new Tamper Resistant requirements for 2008 NEC Section 406.11. Provides additional protection from burns and other injuries. Mandated for residential applications.

Available in 3' & 5' [914mm & 1.5m] lengths with 6" [305mm] receptacle spacing. Provides additional power access in smaller, more confined areas. Multiple lengths present more mounting options.

Steel or aluminum construction. Superior strength for residential applications. Providing years of protection and convenience.

Multiple finishes. Available in ivory, gray, white, black, stainless steel and anodized aluminum to accommodate a wide range of applications.

Custom options available. Custom configurations and finish options are also available. Consult the factory for more information.

This product meets the material restrictions of RoHS.

Built-in shutter system. Prevents the insertion of unwanted objects such as hairpins, keys and nails. Providing additional protection for occupants including small children.

15A Proprietary Simplex Decorator Receptacle. Functional and aesthetically pleasing, matches any décor.

Designed for surface mounting. Easier and more convenient installation. Eliminates the need to break through walls.

Multiple power feed options. Provide clean, attractive installations with concealed power sources.

cULus Listed.

Specifications

General Info

Color	Black	UPC Number	786776174854
Country Of Origin	United States	Product Line	Wiremold
Application Sector	Residential/Commercial	Type	Plugmold
Number of Receptacles	10	Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7

Dimensions

Product Volume US	62.1 cu in	Product Width US	60.0 in
-------------------	------------	------------------	---------

Product Height US	1.38 in	Product Weight US	2.93 lb
-------------------	---------	-------------------	---------

Product Depth US	0.75 in
------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	E15191
--------------	-----	---------------------	--------

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

Technical Information

Voltage	125 V	Frequency Rating	60 Hz
---------	-------	------------------	-------

Enclosure Type	Steel	Environmental Conditions	Dry interior locations
----------------	-------	--------------------------	------------------------
