



Wiremold  
Field Wired deQuorum Single Flip Up Unit with USB  
Part No. DQFF15UST



Field wired unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Comes with a brushed stainless steel finish.

## Features & Benefits

**Sleek, Attractive Design:** Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

**Tamper-Resistant Receptacles:** Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

**New Soft Opening Cover Mechanism:** Opening and closing the cover is quieter and easier with a more professional feel.

**Expanded Configuration Options:** Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

**UL Spill Water Protection:** Meets or exceeds UL 111 - Outline of Investigation for Multioutlet Assemblies. Eliminates risk of shock or short circuiting due to moisture entering device.

**USB Charging Capability:** Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

**Multiple Cover Finish Options:** Durable black powder coat and brushed stainless steel finishes blend with most decors.

**cULus Listed:** Meets UL US and Canadian Safety standards for Multioutlet Assemblies (File E15191, Guide PVGT).

## Specifications

### General Info

|                    |            |              |   |
|--------------------|------------|--------------|---|
| Product Line       | Wiremold   | UPC Number   | 786776186819  |
| Country Of Origin  | Mexico     | Construction | Various   |
| Application Sector | Commercial | Standard     | cULus Multioutlet Assembly File E15191 Guide PVGT Listed to US and Canadian Safety Standards. Meets Article 390 of the NEC. |
| Type               | Flip Up    |              |   |

### Dimensions

|                                       |         |                   |             |
|---------------------------------------|---------|-------------------|-------------|
| Product Width US                      | 4.75 in | Product Length US | 5.625 in    |
| Knockout Size                         | 1/2 in  | Cubic Capacity    | 50.19 cu in |
| Listing Agencies / 3rd Party Agencies |         |                   |             |
| cULus ListingNumber                   | E15191  | cULus Listed      | Yes         |
| Buy American Act Compliance           |         |                   |             |
| NAFTA                                 | Yes     |                   |             |
| Additional Information                |         |                   |             |
| RoHS Conformant                       | Yes     |                   |             |
| Technical Information                 |         |                   |             |
| Cable Entry                           | Bottom  | Mounting Type     | Recessed    |
| Number of Outlets                     | 2       |                   |             |