



Wiremold
Cord Ended deQuorum™ Single Flip Up Unit with USB
Part No. DQFP15UST



Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Unit comes with a 6' (1.83m) cord. Comes with a brushed stainless steel finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XYBS) and Multitoutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

| | | | |
|--------------------|-------------------------|--------------|---|
| Product Line | Wiremold | UPC Number | 786776184563 |
| Country Of Origin | Mexico | Construction | Die Cast |
| Application Sector | Commercial, Residential | Standard | cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC |
| Type | Flip Up | | |

Dimensions

| | | | |
|------------------|---------|-------------------|--------|
| Product Width US | 4.75 in | Product Weight US | 3.9 lb |
|------------------|---------|-------------------|--------|

| | |
|-------------------|----------|
| Product Length US | 5.625 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|-------------|-------|---------------|----------|
| Cable Entry | Below | Mounting Type | Recessed |
|-------------|-------|---------------|----------|

| | |
|-------------------|---|
| Number of Outlets | 2 |
|-------------------|---|
