



Ortronics  
**MM20 CHANNEL RACK - 8FT X 16.25 in - WHITE - 3/8 in SQUARE HOLE**  
 Part No. MM2081638-W



The mighty mo 20 channel racks are designed to provide the greatest in cable management flexibility and efficiency. Honeycomb cutout sidewall allow for infinite cable pathways. The universal 3/8" square hole punch enables mounting of all standard cage nuts and OEM quick mount slides and rails. This creates the industries most versatile equipment rack system.

## Features & Benefits

- Many option for all applications: 5 depths, square hole with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual or tapped hole configurations
- Built-in top trough with waterfalls: Gives bend radius control and cable routing.
- Speed nuts included: Increases speed and ease of assembly, while adding extra strength to your rack-- Speednut eliminates the need for a second wrench.
- Large range of accessories
- Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws: Do not have to purchase as separate items- money saving.
- Open channels top and bottom: Allows floor and ceiling access for horizontal distribution cables.
- Vertical management solutions: A solution for every application-cage with rack unit fingers & hinged slam latch door, cage with rack unit fingers & snap-on covers, cage with hinged latches, and individual cable management rings.
- Can be assembled as a 19" or 23" rack: No additional hardware required- no need to stock two sizes of racks.
- Easy Installation: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack
- Cablofil® ready cable tray & runway brackets
- Honeycomb side rails designed to maximize the airflow of network equipment: Combined with baffles, manages intake and exhaust air creating cold aisle/hot aisle distribution from side vented equipment.

## Specifications

### General Info

Product Line	Ortronics	Color	White
Finish	Powder Coat	UPC Number	662875836414
Country Of Origin	United States	Included	Hardware for mounting
Application Sector	Commercial	Standard	UL 2416

---

Warranty Type	5-Year	Type	Rack
---------------	--------	------	------

---

### Dimensions

---

Product Width US	23.75 in	Product Weight US	42.56 lb
Product Depth US	26.25 in	Product Height US	98.0 in
Rack Depth	26.25 in		

---

### Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

### Technical Information

---

Compatibility	Mighty Mo	Rack Units	51 U
Load Capacity	2000 lb	Cable Entry	Back, Front
Frame	Channel	Mounting	Floor

---