




Wiremold
Plugmold NM2400 Multi-outlet Strips 12"
Part No. NM24GBA612



Nonmetallic Plugmold with alternating circuits. 6' in length with receptacles spaced 12" on center. Nonmetallic plugmold has a textured finish ivory finish, For use with 20 amp circuits.

Features & Benefits

Nonmetallic, lightweight with snap-on cover. Speeds installation: provides easy access to wiring for changes or additions.

Full range of fittings. Facilitates easy installation of wiring for whatever the job: communication workstation outlets, receptacles, switches and more. Over lapping fittings permit neat butting to raceway.

NEMA heavy duty duplex receptacles independently tested to Fed. Spec. WC596G performance criteria. Enhanced product quality ensures dependable performance.

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

Customization available. All products can be modified to accommodate virtually any application.

Tapered profile design with textured ivory finish. Blends with surroundings in office, display space, dorm rooms and residential locations.

Factory wired harness available with duplex receptacles on multiple spacings. Maximum power distribution to the point of use.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates the need for multiple splicing, speeding up installations on long runs.

Field replaceable surge module. No need to remove the raceway cover to splice in a replacement receptacle. Field changes and maintenance are quick and easy.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776520262
Country Of Origin	United States	Number of Receptacles	6

Application Sector	Commercial	Standard	cULus Listed Base & Blank Cover: File E90378 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E90377 GuideRJPR. Base & Blank Cover & Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.
--------------------	------------	----------	---

Type	Plugmold
------	----------

Dimensions

Product Width US	1.75 in	Product Weight US	3.4 lb
Product Depth US	1.0 in	Product Length US	1.75 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Amperage	15 A	Enclosure Type	Non-Metallic
Voltage	120.0 V	Environmental Conditions	Dry interior locations