



radiant Collection  
radiant® 15W USB Outlet, Type C, 15A, Tamper-Resistant, Light Almond  
Part No. R26USBBC6LA



Charge phones, tablets and more up to 40% faster, with USB Outlets from the radiant® Collection. With an industry-leading 30W of power supplying its two included USB Type-C connections, this outlet helps you get that full battery feeling with convenience and speed – no bulky adapters needed. Easily replacing traditional outlets in as little as ten minutes, the USB updates your space with advanced functionality and the sleek, clean lines of radiant for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Provides fast and convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Accommodates the latest mobile devices with two USB Type-C connections.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Features an industry-leading 6.0A of power, as well as Smart Chip technology, to maximize charging speed for each USB connection.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                       |                                |                    |   |
|-----------------------|--------------------------------|--------------------|---|
| Product Line          | Pass & Seymour                 | Color              | Light Almond                                  |
| UPC Number            | 785007207651                   | Country Of Origin  | China   |
| Number of Receptacles | 2                              | Features           | USB-C Charging                                |
| Outlet Type           | Tamper-Resistant, USB-Charging | Application Sector | Hospitality, Multi-Dwelling Unit, Residential |
| Wall Plate Included   | No                             | Warranty Type      | Limited Lifetime Warranty                     |
| Type                  | Outlet                         |                    |   |

Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.693 in | Product Depth US | 1.35 in |
| Product Height US | 4.18 in  |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |             |                      |   |
|---------------------|-------------|----------------------|---|
| Is Tamper-Resistant | Yes         | Connection Location  | Back and Side                             |
| USB Wattage         | 15 W        | USB Amperage         | 6 A                                       |
| Number of USBs      | 2           | Number of Wires      | 3   |
| USB Power Output    | 15 W        | Amperage             | 15 A                                      |
| Number of Poles     | Double Pole | Indoor/Outdoor       | Indoor                                    |
| Mounting Type       | Box         | Wire Connection Type | Internal Pressure Plates, Screw Terminals |
| Voltage             | 5.0 V       |                      |   |