



Wiremold
RC9AFFTC Furniture Feed Poke-Thru Assembly, Black
Part No. RC9AFFTCBK



Complete with hexagonal service head. Service head has one 3/4inch trade size threaded conduit hub and five rubber grommets. The service head includes scrub water gasket. Unit is supplied with one 1 1/4inch and one 1/2inch trade size conduit stem to feed power and communication services. Service head is not to be used as a junction box. All power connections must be made in a junction box below (not supplied). Colors available in painted gray (GY), and painted black (BK). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC9AFFTC Series Poke-Thru Devices require a 3inch (76mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Features & Benefits

Complete with hexagonal service head. Service head has one 3/4inch trade size threaded conduit hub and five rubber grommets.

Service head is not to be used as a junction box. All power connections must be made in a junction box below (not supplied).

RC9AFFTC Series Poke-Thru Devices require a 3inch (76mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

The service head includes scrub water gasket. Unit is supplied with one 1 1/4inch and one 1/2inch trade size conduit stem to feed power and communication services.

Colors available in painted gray (GY), and painted black (BK). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564021704	Country Of Origin	Mexico
Cover Style	Furniture Feed	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		

Dimensions

Product Width US	7.0 in	Product Weight US	5.18 lb
------------------	--------	-------------------	---------

Product Volume US	707.56 cu in	Product Depth US	14.44 in
-------------------	--------------	------------------	----------

Product Height US	7.0 in	Core Hole Size	3 in
-------------------	--------	----------------	------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Carpet, Tile	Service Capacity	Dual
------------	--------------	------------------	------

Fire Rating	2 hr
-------------	------
