




**Wiremold**  
**Resource RFB® Series Two Gang On-Grade Floor Box**  
Part No. RFB2-OG



Resource RFB® Series of Floor Boxes are versatile recessed activation solutions that provide power, communication and/or audio/video services to open space areas, or directly to workstations. Resource RFB Series Floor Boxes are available in two- to six-gang models with a variety of aesthetic cover options including colors and profiles available. Resource RFB Series Floor Boxes have many applications, including schools, financial institutions, commercial office buildings, hospitality and residences.

## Features & Benefits

Resource RFB® Series Two Gang On-Grade Floor Box is a versatile activation solution that provides power and/or communication services to open space areas or directly to the workstation. For use in either on-grade or above grade concrete floors, it is fully adjustable with a tunnel compartment. Supplied with one (1) duplex receptacle mounting plate, and one (1) communication mounting plate. Other device plates sold separately. RFB Series Floor Boxes are now available with the new FloorPort Activation Covers. This new cover series incorporates TopGuard protection to prevent water, dirt, and debris from entering the power and communication devices. The FloorPort Activation Covers are UL Listed to U.S. and Canadian safety standards for tile, terrazzo, carpet, and wood floors. The RFB Series has many unique applications, some of which include schools, financial institutions, commercial office buildings, and residences.

## Specifications

### General Info

Product Line	Wiremold	Replaced by Part Number	RFBA2R300G
Color	Green	UPC Number	786564093459
Country Of Origin	Mexico	Construction	Assembled
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT, Meets Article 314.27(C) of NEC.
Type	Floor Box		

### Dimensions

Product Width US	8.0 in	Product Weight US	8.31 lb
------------------	--------	-------------------	---------

---

Product Volume US	409.64 cu in	Product Depth US	14.63 in
-------------------	--------------	------------------	----------

---

Product Height US	3.5 in	Cubic Capacity	100.4 cu in
-------------------	--------	----------------	-------------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

### Additional Information

---

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

### Technical Information

---

Cable Entry	Knockouts in	Number of Outlets	0
-------------	--------------	-------------------	---

---