




**Wiremold**  
**FLUSH POKE-THRU ASSY/20A/BS/RT/LJB**  
Part No. RC7ATCBS-LJB



Flush Style Poke-Thru Devices are an excellent solution for bringing power, communication, and A/V services to the workstation in an open space, above-grade floor environment. All Wiremold Flush Style Poke-Thru Devices come with built-in TopGuard™ protection, an industry-leading design that meets and exceeds UL scrub water exclusion requirements for tile and carpet floors. Topguard protection prevents water, dirt, or debris from entering not just the power devices, but also the communication devices. All Wiremold Flush Style Poke-Thru Devices can be installed on tile, carpet, or wood covered floors. Each of these devices provides an excellent solution for both new or retrofit construction, with typical applications that include office buildings, airports, malls, shopping centers, libraries, and schools.

## Features & Benefits

Prewired 20A duplex receptacle can be wired as standard duplex or isolated ground.

Wiremold Open System unloaded inserts to accept two discrete keystone connectors from most manufacturers are provided. Includes 2 Cat 6 TechChoice™ discrete keystone connectors and Ortronics® TracJack bezels

## Specifications

### General Info

|                    |  |              |                                |
|--------------------|--|--------------|--------------------------------|
| Product Line       | Wiremold   | UPC Number   | 786564151524                   |
| Country Of Origin  | Mexico   | Construction | Assembled                      |
| Application Sector | Commercial, Education, Healthcare, Hospitality       | Standard     | UL Fire Classified, cULus, NEC |
| Warranty Type      | 1-Year from Installation or 2-Years from Day of Sale | Type         | Poke-Thru                      |

### Dimensions

|                   |          |                |      |
|-------------------|----------|----------------|------|
| Product Weight US | 4.892 lb | Core Hole Size | 3 in |
|-------------------|----------|----------------|------|

### Listing Agencies / 3rd Party Agencies

|                     |       |              |     |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | E2961 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

### Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

## Technical Information

---

|                  |   |                   |      |
|------------------|---|-------------------|------|
| Floor Type       | Carpet, Tile  | Is Pre-Wired      | Yes  |
| Service Capacity | Dual  | Fire Rating       | 2 hr |
| Cable Entry      | 3/4 in conduits stem for power and 2-1/2 in feed openings for low voltage | Number of Outlets | 2    |

---