



All communication device accepts up to four UTP connectors. Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS). Aluminum and brass flanges shipped with black cover. Brass flange also available with brass colored cover assembly (AB). Aluminum flange also available with aluminum colored cover assembly (AA). Unit includes two (2) Ortronics TracJack adapters, two (2) Ortronics Series II adapters, and two (2) Wiremold Open System adapters. Modular jacks sold separately. NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters. RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Features & Benefits

All communication device accepts up to four UTP connectors	Flange available in painted gray (GY), black (BK), ivory (VY), and brushed metal finishes in aluminum (AL) and brass (BS)
Aluminum and brass flanges shipped with black cover	Brass flange also available with brass colored cover assembly (AB)
Aluminum flange also available with aluminum colored cover assembly (AA)	Modular jacks sold separately
Modular jacks sold separately	NOTE: Includes two Cat 6 TechChoice discrete keystone connectors, two Ortronics TracJack adapters, and two Wiremold Open System adapters
RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole	Not designed to work with bare concrete or terrazzo
Floor covering thickness 1/8" minimum	RC9AMD Series Poke-Thru Devices require a 3 1/16" (78mm) diameter hole

Specifications

General Info

Product Line	Wiremold	UPC Number	786564006695
Country Of Origin	Mexico	Construction	Assembled
Cover Style	Surface	Number of Knockouts	1
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru

Dimensions

Product Width US	7.0 in	Product Weight US	4.269 lb
Product Height US	10.0 in	Core Hole Size	3 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Carpet, Tile	Service Capacity	Dual
Fire Rating	2 hr	Cable Entry	Conduit