



radiant Collection  
radiant® Single Pole 3-Way Occupancy Sensor, Black  
Part No. RRW600UBK



Simplify control while saving energy, with the radiant® Occupancy Sensor. Automatically turning the light on when someone enters a room, and shutting it off when the room is empty, this sensor includes an adjustable timed delay for shut off, as well as additional settings for more flexible control. Part of the radiant® Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Passive infrared (PIR) sensor switch technology with 180° coverage up to 600 sq. ft. Rated for up to 600W (5A) of LED lighting.

Turn the light on when you enter, and let it turn itself off automatically after you leave for true convenience. Perfect for bathrooms, hallways, closets, garages, and more.

Features an adjustable time delay to off after no motion is detected. Delay settings range from 30 seconds to 20 minutes after the room is vacated (default 5 minute delay).

Replace any basic light or fan switch in 15 minutes or less. Supports single pole and multi-location installs. No neutral required.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Works with virtually any bulb/fixture, including: LED, incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Auto ON/Auto OFF functionality as default. Easily configurable to Manual ON/Auto OFF to meet any need or preference in the home.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Features	Motion Sensor
Switch Type	Motion Sensor	Application Sector	Residential

### Dimensions

Product Width US	1.69 in	Product Depth US	1.88 in
------------------	---------	------------------	---------

---

Product Height US            2.63 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed                Yes

---

### Technical Information

---

Target Size	180 deg	Response Frequency	60 Hz
-------------	---------	--------------------	-------

---

Sensor Type	Occupancy	Amperage	5 A
-------------	-----------	----------	-----

---

Number of Poles	Single Pole 3-Way	Indoor/Outdoor	Indoor
-----------------	-------------------	----------------	--------

---

Wattage	600 W	Mounting Type	Box
---------	-------	---------------	-----

---

Sensing Range	600 sq ft	Voltage	120 V
---------------	-----------	---------	-------

---

Sensitivity	60Hz	Load	120VAC
-------------	------	------	--------

---