



Pass and Seymour
Smart Plug-In Tru-Universal Dimmer with Netatmo
Part No. WNP20



The smartest way to take control of lights and power, optimized for larger homes. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, dimmers and outlets to build a solution that perfectly fits a homes unique space and needs. Options include wireless smart switches and dimmers for easily adding 3-way control. The Smart Plug-In Tru-Universal Dimmer works with virtually any 120V dimmable bulb or fixture, adjusting to the precise light level you want, without the flicker. Unsure what dimmer your bulb needs? Avoid uncertainty with Tru-Universal Dimming. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED

Control table and floor lamps from smartphones and tablets* with the Legrand Home + Control app. Even schedule lights to turn on/off automatically, create groups, set scenes and monitor energy usage

Provides dimmable control of table and floor lamps using any 120V dimmable bulb

Features ultra-reliable performance through a robust and dedicated mesh-network

Flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets, including wireless switches and dimmers

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems

Installs easily, no wiring required. Simply plug in to an existing 120V electrical outlet

Can be paired with a Smart Tru-Universal Dimmer or Smart Wireless Dimmer for remote control

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007289770
Country Of Origin	China	Features	Smart Lighting, With Netatmo

Switch Type	Button, Multi-Location, Push, Single Pole 3-Way	Number of Switches	1
Works With	Amazon Alexa, Apple Home Kit, Google Assistant	Application Sector	Hospitality, Residential
Warranty Type	1-Year Limited Warranty	Type	Dimmer
Dimensions			
Product Width US	3.0 in	Product Height US	2.0 in
Product Length US	1.38 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E495025	cULus Listed	Yes
FCC Compliant	Yes		
Additional Information			
RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Technical Information			
Load Rating	120V 250W 2.1A (CFL - Reverse Phase Only), 120V 250W 2.1A (EFL - Reverse Phase Only), 120V 250W 2.1A (ELV - Reverse Phase Only), 120V 250W 2.1A (LED - Reverse Phase Only), 120V 450W (ELV - Reverse Phase Only), 120V 450W (Halogen - Reverse Phase Only), 120V 450W (Incandescent - Reverse Phase Only), 120V 450W 3.8A (CFL - Forward Phase Only), 120V 450W 3.8A (EFL - Forward Phase Only), 120V 450W 3.8A (LED - Forward Phase Only), 120V 700W (Halogen - Forward Phase Only), 120V 700W (Incandescent - Forward Phase Only)	Dimming Compatibility	Forward or Reverse Selectable Phase

Frequency Rating	60 Hz	Bulb Compatibility	CFL, Fluorescent, Halogen, Incandescent, LED
Number of Poles	Multi-Location, Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Plug-in	Wire Connection Type	Plug-In
Voltage	120 VAC		