



The smartest way to take control of lights and power, optimized for whole home use.

Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart light switches, smart dimmer light switches and smart outlets to build a solution that perfectly fits a home's unique space and needs.

Control lights at the wall with this sleek sofTap® switch, or through the intuitive app. Pair this smart switch with the Wireless Smart Switch with Netatmo to gain easy 3-way control.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Smart Gateway REQUIRED	Control lights from smartphones and tablets with the Legrand Home + Control app. Even schedule lights to turn on/off automatically, create groups, set scenes and monitor energy usage
Features ultra-reliable performance through a robust and dedicated mesh-network	Installs easily in place of an existing single-pole switch or dimmer (neutral wire required). For easy 3-way control, pair with a Wireless Smart Switch with Netatmo
Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems	Flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets, including wireless switches and dimmers
Available color options include White, Magnesium, and Graphite	Pair with designer wall plates from the adorne® Collection to fit any style

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007380781
Country Of Origin	China	Number of Switches	1
Application Sector	Residential, Commercial	Warranty Type	1-Year Limited Warranty

---

Type	Switch
------	--------

---

## Dimensions

---

Product Width US	1.73 in	Product Weight US	0.625 lb
------------------	---------	-------------------	----------

---

Product Depth US	1.53 in	Product Height US	4.19 in
------------------	---------	-------------------	---------

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E350248	cULus Listed	Yes
---------------------	---------	--------------	-----

---

## Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

## Technical Information

---

Load Rating	Incandescent / halogen 1800W, Ballast 15A standard / electronic, LED 5A, 1/2 HP motor	Compatibility	Amazon Alexa, Google Assistant, Apple HomeKit
-------------	---	---------------	---

---

Number of Poles	Single Pole, 3-Way, Multi-Location	Supply Voltage	120 VAC
-----------------	------------------------------------	----------------	---------

---

Voltage	120 V	Connection Type	Wired
---------	-------	-----------------	-------

---

Load Type	Incandescent, Halogen, or LED
-----------	-------------------------------

---