



Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, adorne® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer light switches and smart outlets to build a solution that perfectly fits a home's unique space and needs.

Through Tru-Universal technology, this sofTap® smart dimmer switch works with virtually any 120V dimmable bulb or fixture. Pair with an adorne Wireless Smart Dimmer with Netatmo to gain easy 3-way control.

Made exclusively for use with Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Smart Gateway REQUIRED

Control lights from smartphones and tablets with the Legrand Home + Control app. Even schedule lights to turn on/off automatically, create groups, set scenes and monitor energy usage

Works with virtually any 120V dimmable bulb or fixture and installs easily in place of an existing switch (neutral wire required)

Features ultra-reliable performance through a robust and dedicated mesh-network

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems

Flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets, including wireless switches and dimmers

Available color options include White, Magnesium and Pair with designer wall plates from the adorne® Collection to fit any Graphite style

Specifications

General Info

| | | | |
|--------------------|----------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Magnesium |
| Finish | Matte | UPC Number | 785007380828 |
| Country Of Origin | China | Receptacle Type | Double |
| Number of Switches | 1 | Application Sector | Residential, Commercial |

| | | | |
|---------------|-------------------------|------|--------|
| Warranty Type | 1-Year Limited Warranty | Type | Dimmer |
|---------------|-------------------------|------|--------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E95219 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-----------------|-----|
| RoHS Conformant | Yes |
|-----------------|-----|

Technical Information

| | | | |
|-------------|---|---------------|---|
| Load Rating | "Incandescent, Halogen & ELV (FWD): 700W, MLV (FWD) : 500VA, LED/CFL/EFL (FWD): 450W / 3.8A, Incandescent, Halogen & ELV (REV): 450W, LED/CFL/EFL (REV): 250W / 2.1A" | Compatibility | Amazon Alexa, Google Assistant, Apple HomeKit |
|-------------|---|---------------|---|

| | | | |
|-----------------|---|-----------------|------------------------------------|
| Number of Wires | 4 | Number of Poles | Single Pole, 3-Way, Multi-Location |
|-----------------|---|-----------------|------------------------------------|

| | | | |
|---------|-------|----------------|---------|
| Wattage | 700 W | Supply Voltage | 120 VAC |
|---------|-------|----------------|---------|

| | | | |
|---------|-------|-----------------|-------|
| Voltage | 120 V | Connection Type | Wired |
|---------|-------|-----------------|-------|

| | |
|-----------|-----------------------------|
| Load Type | Incandescent, Halogen & ELV |
|-----------|-----------------------------|
