




radiant Collection
radiant® Wireless Smart Dimmer with Netatmo, White
Part No. WNRL63WH



Pair this battery-operated, wireless dimmer with a radiant Smart Tru-Universal Dimmer with Netatmo, then add it to any wall to control the same light from an additional location. No wires or tools needed. Use the included adhesive to mount anywhere in minutes. Perfect as a remote dimmer switch in rooms not wired for 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, smart dimmer switches and smart outlets to build a solution that perfectly fits any space and need. Screwless Wall Plates from the radiant® Collection included.

Features & Benefits

Smart Gateway REQUIRED. Must also be paired with an adorne or radiant Smart Tru-Universal Dimmer with Netatmo or a Smart Plug-In Tru-Universal Dimmer with Netatmo.

Installs easily, without wires or cutting, for ultimate flexibility. Simply mount to any wall for long-lasting, battery-powered control.

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Perfect solution for adding 3-way control, no wiring required, when paired with a Smart Tru-Universal Dimmer with Netatmo.

Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including other wireless switches and dimmers).

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look

Specifications

General Info

| | | | |
|-------------------|----------------|------------|---|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007289732 |
| Country Of Origin | China | Features | Locator Light, Smart Lighting, Wireless, With Netatmo |

| | | | |
|---------------------------------------|--|---|--------------------------|
| Switch Type | Paddle | Number of Switches | 1 |
| Works With | Amazon Alexa, Apple Home Kit, Google Assistant | Application Sector | Hospitality, Residential |
| Warranty Type | 1-Year Limited Warranty | Type | Dimmer |
| Dimensions | | | |
| Product Width US | 1.73 in | Product Height US | 4.19 in |
| Product Length US | 1.53 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | E95219 | cULus Listed | Yes |
| FCC Compliant | Yes | | |
| Additional Information | | | |
| RoHS Compliant | Yes | Product Has Potential to Contribute to LEED | Yes |
| Technical Information | | | |
| Seismic Tested | No | Dimming Compatibility | Wireless |
| Frequency Rating | 2.4 to 2.4835 GHz | Number of Poles | Multi-Location |
| Wire Size | #14 - #10 AWG | Requires Neutral Wire | No |
| Indoor/Outdoor | Indoor | Mounting Type | Surface Mount, Wall Box |
| Wire Connection Type | Battery Powered | Voltage | 3.0 V |