CORRIDOR CEILING INTEGRATED SENSOR

DALI-2SEN-LSPD-O-CI

Mounting Options:
Ceiling Integration, Flush Mount to Junction Box, or Surface Mount with optional Mounting Adapter kit

Passive Infrared (PIR) and Photo Sensors

Detection Range up to 12 m (39.4 ft)

DESCRIPTION

The Wattstopper PLUS DALI-2 LS PD O CI Sensor utilizes Passive Infrared (PIR) and Photo Sensors to provide occupancy and light information.

The compact IP20 rated housing designed for integration into recessed ceilings make this sensor ideal for office applications.

The DALI-2 LS PD O CI Sensor is DALI-2 certified and communicates with the Wired Manger – DALI, a key component of the Wattstopper PLUS System.

FEATURES

- Designed for easy ceiling integration with the attached mounting clip
- Wide motion detection range optimized for offices up to 12 m (39.4 ft)
- Mounting height up to 4 m (13.1 ft)
- Includes mounting plate for flush mounting to junction box
- Easily adaptable to surface mounting with the use of the optional Mounting Adapter Kit
- DALI-2 certification

SPECIFICATIONS

- Voltage: 16 VDC, via DALI
- Current Consumption: 8mA
- Light Sensor Operating Range: Up to 1,500 lux (measured at sensor)
- Weight: 120 g (4.2 oz)
- Operating Temperature: -4° to 113°F (-20° to 45°C)
- Relative Humidity: 5% to 85%, non-condensing
- Certifications: CE, DALI2
- Complies with Electromagnetic Compatibility (EMC) Standards:
  - EN 55015, EN 61347-1, EN 61347-2-11, EN 61547,
  - EN 62386-101, EN 62386-103, EN 62386-303,
  - EN 62386-304, EN IEC 63000
- Environmental Suitability: IP20
- 5 year warranty

PROJECT		LOCATION/ TYPE	

DIMENSIONS

Sensor



Mounting Adapter Kit



SYSTEM OVERVIEW

Wattstopper PLUS enables you to control DALI devices. With any Wattstopper PLUS wired design, you get a reliable, lighting control system that can be installed quickly and easily.



MOUNTING

Ceiling Integration



Surface Mount (with optional Mounting Adapter Kit)



Flush Mount



WIRING



SENSOR DETECTION RANGE



	Mounting Height			
	2 m (6.6 ft)	2.5 m (8.2 ft)	3 m (10 ft)	4 m (13.1 ft)
Detection Type	**Detection Range**			
Presence	3 m (9.8 ft)	4 m (13.1 ft)	4.5 m (14.8 ft)	—
Motion	6 m (19.6 ft)	8 m (26.2 ft)	9 m (29.5 ft)	12 m (39.4 ft)

ORDERING INFORMATION

Catalog #	Description	Communication Network
☐ DALI-2SEN-LSPD-O-CI	DALI-2 LS PD O CI Sensor	Wired DALI-2
☐ QBM220240-LSPD-CMKIT	Mounting Adapter Kit	N/A

34696r1 Rev 04/25