

EQUINOX 73 LCD TOUCHSCREEN

EQ73TB-TI-III / EQ73TB-NI-III

Weather mini widget provides real-time local weather

Hardwired, always connected, always on multi-system dashboard (showing lighting, scenes, and climate system status via on-screen widgets)

Glass to edge aesthetic and graphical user interface

Home button returns to the main page, no matter where you are in the navigation



Personalized by user, location, etc.

“Press” the discovery dots for more information, more control, and the ability to create and edit widget functions

Simple, intuitive graphical user interface for multi-system control

Programmable tactile switch can provide traditional “on” or “off” function, personalized scene control, etc.

Swipe left or right at the dashboard level to reveal other system widgets

DESCRIPTION

Equinox 73 is a high bright LCD touchscreen that is always on and always available. The touchscreen provides immediate control and status for three sub-systems via three vibrant widgets at a time. It offers a simple, smart tablet type navigation experience with complete consistency across EQ41 touchscreens, EQ 40 keypads, and EQ apps for mobile devices. The EQ 73 dashboard view (homescreen) offers immediate status and control of day to day functions. Navigate to the second or full screen layer for more specific, less used operations. The edit mode layer is then used for users to schedule and update pre-defined tasks.

OPERATION

Utilizing the combined power of InFusion and Design Center software, Equinox 73 can be auto configured with subsequent updates delivered through Design Center or on the EQ 73 screen. The pre-defined graphical environment allows installers and programmers to efficiently create intuitive screens that are consistent with the entire user environment. With the unique profiles feature, users are given the ability to personalize their experience. The touchscreen gives users the ultimate power by allowing them to schedule, edit, and prioritize the control functions that matter most to them.

HIGHLIGHTS


A 7” LCD touchscreen truly sets EQ 73 apart. With a larger screen, users are able to view three widgets at a time and easily navigate in full screen and edit modes. And since all Equinox products maintain a consistent, sleek appearance, Equinox 73 looks beautiful on the wall. This touchscreen gives the user ultimate control over his/her environment by allowing him/her to edit or create new scenes. Within every widget, there are options for changing or creating new functionality based on the needs and desires of the end user.

APPLICATIONS


Equinox 73 is the perfect addition to any automated lighting project running Vantage’s InFusion system. With its ability to access and control sub-systems via on-screen widgets, EQ 73 is a necessity for spaces with automated lighting control. When the requirements of the space indicate the need for a quick dashboard view of multiple sub-systems, EQ 73 should be a primary consideration. The 7” screen also makes EQ 73 ideal for working in the full screen and edit modes, so users who desire this feature should include EQ 73 in their solution as well.

PROJECT		LOCATION/ TYPE	
---------	--	-------------------	--


MULTI-VIEW LINE DRAWING




TOP VIEW




SIDE VIEW




FRONT VIEW



BACK VIEW



SIDE VIEW



BOTTOM VIEW

FEATURES


- 7" LCD touchscreen
- Titanium or Nickel TrimLine II frame; black glass-to-edge surface aesthetic
- Unique widget based graphical user interface
- Aesthetically identical to other Equinox products
- Ambient light sensor for auto day/night backlighting
- Each Equinox device includes one software license for the Equinox app
- Motion sensor screen on and initiate task
- Three visible widgets with full screen and edit modes
- 90% daily control; customize through additional screen levels
- Gesture, flick, tap, and swipe
- Aesthetic and user interface consistency with Equinox 41 and tablet apps (Android and iOS)

SPECIFICATIONS


Dimensions - On-Wall Surface (HWD):	4.9" x 6.9" x 0.37" (124mm x 175mm x 9mm)
Dimensions - Overall (HWD):	4.9" x 6.9" x 2.1" (124mm x 175mm x 53mm)
Model:	EQ73TB-TI-III, EQ73TB-NI-III
Weight:	1.6 lb (725.75g)
Display:	Active matrix color LCD
Display Size:	7" diagonal
Display Resolution:	1024 x 600 pixels
Hard Buttons:	Left: Home; Right: Programmable
Power:	PoE
Surge Suppression:	Yes
Sound Option:	Adjustable volume level - touch interaction
Wiring Connections:	Communication: Ethernet RJ45 or WiFi dongle
Power:	PoE/PoE+
Addressing:	Self addressing through software
Finishes:	Trim: Titanium (TI), Nickel (NI) Touchscreen: Black glass
Glass Surface:	Chemically strengthened
Ambient Operating Temperature:	32°F - 95°F (0°C - 35°C)
Ambient Operating Humidity:	5 - 95% non-condensing
Licensing:	Each Equinox device includes one software license for the Equinox app
System Compatibility:	InFusion, Design Center 3.9.2.590 and above
Certification:	CE, UKCA, EN 55032, EN 55035, EN 61000-3-2, EN 61000-3-3, EN 62368-1, EN 60065

WIDGET OPTIONS

See widget cutsheet for additional details.




WIRING AND POWER DIAGRAM



EQUINOX 73 ILLUSTRATION AT VARIOUS ANGLES

Please reference local and NEC codes for appropriate electrical and communication install methodology



ORDERING INFORMATION

Catalog #	Description	Voltage / Misc.
<input type="checkbox"/> EQ73TB-TI-III	Equinox 73 LCD Touchscreen - Titanium	PoE
<input type="checkbox"/> EQ73TB-NI-III	Equinox 73 LCD Touchscreen - Nickel	PoE
<input type="checkbox"/> EQ73ST-INSTALL	Equinox 73 LCD Standard Install Kit	
<input type="checkbox"/> EQ73RE-INSTALL	Equinox 73 LCD Retrofit Install Kit	
<input type="checkbox"/> EQ41TB-TI-II	Equinox 41 LCD Touchscreen	12VDC via PoE
<input type="checkbox"/> EQ-APP-5	Equinox 1-5 App License SD Card	
<input type="checkbox"/> EQ-APP-10	Equinox 1-10 App License SD Card	
<input type="checkbox"/> EQ-APP-X	Equinox Unlimited App License SD Card	