Installer-Friendly Features



Rear stabilizer legs
- Rest against opposing wallboard.
- Control the depth that a box can flex.
- Maintain device rigidity during plug insertion.
- Heavy cross section minimizes wallboard damage.

Side stabilizer tabs
- Keep box from flexing out when plug is removed abruptly.
- Permits use of phantom studs.





Height sight
- Centers box on your reference mark.

Bracket countersink
- Allows #8 waferhead or sheet rock screws with minimal wallboard bow.

Box levelers
- Automatically align box at right angle to stud.

The original Quick/Click®
- Unique, labor-saving design secures device quickly and easily.
- Simply push in and turn the screw one turn.
- Does not strip when over-torqued.

For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/passandseymour. We're eager to put our expertise to work for you.

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-776-4035
www.legrand.us/passandseymour

©2010, Legrand/Pass & Seymour BR1381 7/07 AGI/DG

Distributed by:

legrand®

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

P&S Boxes

PRODUCT OFFERING HIGHLIGHTS INCLUDING NEW PRODUCTS AND FEATURES SPRING 2006

legrand®

Pass & Seymour

designed to be better.

Contractor-inspired innovative solutions

From the advice of electrical professionals, P&S has a long history of designing innovation into our Box offering for:
- **large volume**
- **easy installation**
- **better performance**
- **increased productivity**
- **fewer call backs**

In 1973, P&S introduced the original Quick/Click® into the Box line which does all of the above and eliminates device mounting hole strip out.

Now meet the next series of contractor requested features. Proof-positive that Pass & Seymour is proud to be "the one that works for you®."

Wall Boxes

New Construction

- Quick/Click® feature* secures device quickly and easily. Does not strip when over-torqued.
- Largest box volumes in class.
- Rear stabilizer legs and side stabilizer tab.
- Height sight, bracket countersink, and box levelers.

S1-22-B*
P1-22-B

SH1-22-B*
PH1-22-B

S1-22-C*
P1-22-C

SH1-22-R*
PH1-22-R

S1-22-R*

S2-35-RAC*

S3-54-RAC*

S4-68-RAC*

Old Work

- Quick/Click® feature* secures device quickly and easily. Does not strip when over-torqued.
- Metal swing brackets permit installation of box in wall with 1-1/4" thick wallboard down to 1/8" thick paneling.

S1-16-W*

P1-16-W

S1-18-W*

*Quick/Click feature on catalog numbers beginning with "S" only.

Range & Dryer Boxes

- Factory-installed, internal metallic wire clamp provides dependable strain relief.
- Large cable entry accommodates up to #6 gauge copper or aluminum wire.
- Rear stabilizer legs and side stabilizer tab.
- Height sight, bracket countersink, and box levelers.
- Large 42 cubic inch volume.

P2-42-RRD

P2-42-SRD

4" Square Junction Boxes

- Two factory-installed #8 screws for easy mud ring installation (accepts standard P&S mud rings RC1, RC2, or 4SBC).
- Height sight and bracket countersink.
- Shallow 1/4" depth ideal for masonry-furring strip style walls.

S44-18-BAC

Extension Rings

A box that is set back too far? No problem! Use a set of extension rings that allow trim-out adjustment.

- 1/4" thick.
- Stackable for any depth.
- Can be modified to accommodate three- or four-gang applications.

EXT1

EXT2

Low-Voltage Brackets & Divider

- Available in single, 2- and 3-gang, new construction and old work style.
- Old work style has unique alignment feature and metal swing brackets.
- Robust design with spacious openings.



Floor Boxes

- Available in single, 2-gang and round, low-voltage, line voltage and dual-voltage.
- Products suitable for wood or concrete sub-floors.
- Nickel, aluminum or brass finish plates.
- Scrub-water compliant.

FB1SRKS

PS863PCOMAL

Ceiling Boxes

Nail-On & Direct Mount Boxes

- UL-Listed for fan and fixture support.
- Dual mounting accommodates either 2.75" or 3.5".
- Screw lock on direct mount boxes holds screws in box until needed so there's no lost hardware — and away from spiral saws so there are no broken bits.

S1-20-RFAN

S1-16-FAN

S1-09-FAN

Metallic Ceiling Boxes & Braces

- Exclusive rotating dual supports for fan and fixtures.
- Broadest line available with convenient top and side knockouts.

77706

55505

55025



55501

22200

For the complete offering of P&S Boxes, see catalog sections P and Q or visit us at www.legrand.us/passandseymour.