




Pass & Seymour

Weatherproof Boxes & Covers Heavy Cast Aluminum Covers Flush Enclosures

4600, 4600-1P, 4600-7P, 4600-8P, 4600-26P, 4609

Lock out weather — and unauthorized users.

These heavy aluminum covers keep weather out with neoprene gaskets — and unauthorized users out with a sturdy cam lock. Each cover comes with two keys. In addition to the mounting screws that secure covers to the box, these rugged covers lock into walls via mortar keys.



Features & Benefits

Adapter, frame and cover are heavy cast aluminum.

Neoprene gasket seals cover to frame so moisture and dust cannot enter.



2 keys provided for cam lock.

Mortar keys provide positive holding means within wall.







#8-32 screws hold assembly firmly in place.

4600

Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

Ordering Information

Catalog Number	Description	Color
Mortared-in Applications		
 4600	Enclosure Only, without Mounting Plate	Gray
 4600-1P	Mounting Plate for Toggle Switch	Gray
 4600-7P	Mounting Plate for Single Receptacle Diameter: 1.406"	Gray
 4600-8P	Mounting Plate for Duplex Receptacle	Gray
 4600-26P	Mounting Plate for Decorator/GFCI	Gray
 4609	Key for Enclosure	—

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Weatherproof Boxes & Covers Heavy Cast Aluminum Covers Flush Enclosures



Pass & Seymour

Technical Specifications

3rd Party Compliance


UL Listed.
CSA Certified.
Complies with 2002 NEC Section 406.8(A) and 406.8(B)(2).

Performance

Environmental Corrosion-Resistant Weatherproof

Materials

Body	.125" Cast Aluminum
Springs	Stainless Steel
Hinges	Plated Steel Pins
Screws	Steel, Zinc-Plated or Aluminum
Gasket	Neoprene
Insert Plates	.086" Aluminum



Dimensions for
Flush Enclosure

Warranty

1 Year

Complementary Devices & Accessories




WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Cast Covers
- Boxes




WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers




SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca