PW Steel Ladder Cable Tray
Horizontal Fitting

90HB
Horizontal 90° Elbow





HORIZONTAL ELBOW CATALOG NUMBERING EXAMPLE

FITTING
SYSTEM NO. PRODUCT NO.

BOTTOM TYPE ← LD - 4G2I - 9024 - 18 → WIDTH

BOTTOM TYPE					WIDTH
VENTED					06 - 6"
LD - Ladder	MATERIAL				09 - 9"
VC! - Vented Corrugated	SIDE RAIL	G	FITTING	FLANGE	12 - 12"
NON-VENTED	HEIGHT	L	SERIES	DIRECTION	18 - 18"
SC! - Solid Corrugated	4 - 4"	T	1 – SERIES 1	I - Flange In	24 - 24"
SF! - Solid Flat Bottom	5 - 5"		2 – SERIES 2	O - Flange Out	30 - 30"
! Available for flange in only	6 - 6"				36 - 36"
VC/SC Available in steel only	7 - 7"				
SF Available in stainless steel only					

PRODUCT NUMBER RADIUS (IN.)	W	R2	SERIES1 A	SERIES1 B	SERIES1 C	SERIES1 D	SERIES2 A	SERIES2 B	SERIES2 C	SERIES2 D
9012 12"	6	18	20	20	34	34	23	23	40	40
	9	21	23	23	37	37	26	26	43	43
	12	24	26	26	40	40	29	29	46	46
	18	30	32	32	46	46	35	35	52	52
	24	36	38	38	52	52	41	41	58	58
	30	42	44	44	58	58	47	47	64	64
	36	48	50	50	64	64	53	53	70	70
9024 24"	6	30	32	32	58	58	35	35	64	64
	9	33	35	35	61	61	38	38	67	67
	12	36	38	38	64	64	41	41	70	70
	18	42	44	44	70	70	47	47	76	76
	24	48	50	50	76	76	53	53	82	82
	30	54	56	56	82	82	59	59	88	88
	36	60	62	62	88	88	65	65	94	94
9036 36"	6	42	44	44	82	82	47	47	88	88
	9	45	47	47	85	85	50	50	91	91
	12	48	50	50	88	88	53	53	94	94
	18	54	56	56	94	94	59	59	100	100
	24	60	62	62	100	100	65	65	106	106
	30	66	68	68	106	106	71	71	112	112
	36	72	74	74	112	112	77	77	118	118

MATERIAL: STEEL/STAINLESS STEEL
FINISH SUFFIX:
G: HOT DIP GALVANIZED STEEL PER ASTM A123
L: 304 STAINLESS STEEL PER ASTM A-240
T: 316 STAINLESS STEEL PER ASTM A-240
BOTTOM: LD - LADDER
VC - VENTED CORRUGATED
SC - SOLID CORRUGATED
SF - SOLID FLAT BOTTOM
Construction: Welded
Tray Design: Tray constructed and markings are per the latest addition of NEMA Standards Publication VE1, CSA C22.2 No. 126
Connectors: All fittings are supplied with necessary connectors and fasteners
Fitting Heights (H): 4", 5", 6", 7"
Tangents: Series 1 fittings have a 2" tangent
Series 2 fittings have a 5" tangent

"Copyright LNA, Inc. Drawings are proprietary and may not be copied or otherwise duplicated or used without express written permission."

CABCS1503

Legrand
8319 State Rt. 4
Mascoutah, IL 62258 USA
800-658-4641
618-566-3250
Fax618-566-4978
www.legrand.us/cablofil