PW Steel Ladder Cable Tray
Horizontal Fitting

L H REDUCER
Horizontal Left Hand Reducer





HORIZONTAL REDUCER CATALOG NUMBERING EXAMPLE

FITTING SYSTEM NO. PRODUCT NO.

BOTTOM TYPE ← **LD - 4G2I - 0718 - 12** → WIDTH

BOTTOM TYPE	MATERIAL				WIDTH
VENTED					**06** - 6"
LD - Ladder					**09** - 9"
VC! - Vented Corrugated	SIDE RAIL HEIGHT	G	FITTING SERIES	FLANGE DIRECTION	**12** - 12"
NON-VENTED		L			**18** - 18"
SC! - Solid Corrugated	**4** - 4"	T	1 – SERIES 1	**I** - Flange In	**24** - 24"
SF! - Solid Flat Bottom	**5** - 5"		2 – SERIES 2	**O** - Flange Out	**30** - 30"
I Available for flange in only	**6** - 6"				**36** - 36"
VC/SC Available in steel only	**7** - 7"				
SF Available in stainless steel only					

MATERIAL: STEEL/STAINLESS STEEL
FINISH SUFFIX:
G: HOT DIP GALVANIZED STEEL PER ASTM A123
L: 304 STAINLESS STEEL PER ASTM A-240
T: 316 STAINLESS STEEL PER ASTM A-240
BOTTOM: LD - LADDER
VC - VENTED CORRUGATED
SC - SOLID CORRUGATED
SF - SOLID FLAT BOTTOM
Construction: Welded
Tray Design: Tray constructed and markings are per the latest addition of NEMA Standards Publication VE1, CSA C22.2 No. 126
Connectors: All fittings are supplied with necessary connectors and fasteners
Fitting Heights (H): 4", 5", 6", 7"
Fitting Length: L=12" for Series 1 fittings
L=18" for Series 2 fittings

MAIN WIDTH (IN.) W1	BRANCH WIDTH (IN.) W2	LEFT HAND
9	6	0709
12	6	0712
	9	0712
18	6	0718
	9	0718
	12	0718
24	6	0724
	9	0724
	12	0724
	18	0724
30	6	0730
	9	0730
	12	0730
	18	0730
	24	0730
36	6	0736
	9	0736
	12	0736
	18	0736
	24	0736
	30	0736

"Copyright LNA, Inc. Drawings are proprietary and may not be copied or otherwise duplicated or used without express written permission."

CABCS1515

Legrand
8319 State Rt. 4
Mascoutah, IL 62258 USA
800-658-4641
618-566-3250
Fax618-566-4978
www.legrand.us/cablofil