PW Steel Ladder Cable Tray
Horizontal Fitting

TEE
Horizontal Tee





HORIZONTAL TEE CATALOG NUMBERING EXAMPLE

FITTING SYSTEM NO. PRODUCT NO.

BOTTOM TYPE ← **LD - 4G2I - 2024 - 18** → WIDTH

BOTTOM TYPE	MATERIAL				WIDTH
VENTED					**06** - 6"
LD - Ladder					**09** - 9"
VC! - Vented Corrugated	SIDE RAIL HEIGHT	G	FITTING SERIES	FLANGE DIRECTION	**12** - 12"
NON-VENTED		L			**18** - 18"
SC! - Solid Corrugated	**4** - 4"	T	1 – SERIES 1	**I** - Flange In	**24** - 24"
SF! - Solid Flat Bottom	**5** - 5"		2 – SERIES 2	**O** - Flange Out	**30** - 30"
! Available for flange in only	**6** - 6"				**36** - 36"
VC/SC Available in steel only	**7** - 7"				
SF Available in stainless steel only					

MATERIAL: STEEL/STAINLESS STEEL
FINISH SUFFIX:
G: HOT DIP GALVANIZED STEEL PER ASTM A123
L: 304 STAINLESS STEEL PER ASTM A-240
T: 316 STAINLESS STEEL PER ASTM A-240
BOTTOM: LD - LADDER
VC - VENTED CORRUGATED
SC - SOLID CORRUGATED
SF - SOLID FLAT BOTTOM
Construction: Welded
Tray Design: Tray constructed and markings are per the latest addition of NEMA Standards Publication VE1, CSA C22.2 No. 126
Connectors: All fittings are supplied with necessary connectors and fasteners
Fitting Heights (H): 4", 5", 6", 7"
Tangents: Series 1 fittings have a 2" tangent
Series 2 fittings have a 5" tangent

PRODUCT NUMBER RADIUS (IN.)	W	SERIES1		SERIES2	
		A	B	A	B
2012 12"	6	34	20	40	23
	9	37	23	43	26
	12	40	26	46	29
	18	46	32	52	35
	24	52	38	58	41
	30	58	44	64	47
	36	64	50	70	53
2024 24"	6	58	32	64	35
	9	61	35	67	38
	12	64	38	70	41
	18	70	44	76	47
	24	76	50	82	53
	30	82	56	88	59
	36	88	62	94	65
2036 36"	6	82	44	88	47
	9	85	47	91	50
	12	88	50	94	53
	18	94	56	100	59
	24	100	62	106	65
	30	106	68	112	71
	36	112	74	118	77

"Copyright LNA, Inc. Drawings are proprietary and may not be copied or otherwise duplicated or used without express written permission."

CABCS1517

Legrand
8319 State Rt. 4
Mascoutah, IL 62258 USA
800-658-4641
618-566-3250
Fax618-566-4978
www.legrand.us/cablofil