



SII – HDJ Bezel

Description

Series II to HDJ Adapter Bezel made from durable thermoplastic. Available in a variety of colors to match your workstation applications. For more information, please contact your local sales representative.

Features & Benefits

- Compatible with any Wiremold Series II insert
- SII faceplate allows users to create most complete AV solution with all footprints

Color	Fog White, Black, Electric Ivory, White, WM Ivory
Country of Origin	Taiwan
Type	SII, HDJ
Standard	UL 1863

Dimensions

Product Width	8 in
Product Height	1 in
Product Depth	1 in

Technical Information

Construction	Plastic
Use Type	Series II to HDJ Adapter Bezel
Compatibility	568A/B
Ports	1, 2
Contact Resistance	<20mOhms
Insertion Loss	<0.45dB@500Mhz
Withstand Voltage	1000 VAC
Operating Temp	-20° - 85° C

Ordering Information

S21HDJ10	SII, 1 HDJ PORTS, 1UNIT, 10PK, FG WHITE
S21HDJ10-00	SII, 1 HDJ PORTS, 1UNIT, 10PK, BLACK
S21HDJ10-13	SII, 1 HDJ PORTS, 1UNIT, 10PK, IVORY
S21HDJ10-88	SII, 1 HDJ PORTS, 1UNIT, 10PK, WHITE
S21HDJ10-99	SII, 1 HDJ PORTS, 1UNIT, 10PK, WM IVORY
S22HDJ10	SII 1U 2 PORT HDJ, 10 FG WHT
S22HDJ10-00	SII 1U 2 PORT HDJ, 10 BLACK
*S22HDJ10-13	SII 1U 2 PORT HDJ, 10 IVORY
S22HDJ10-88	SII 1U 2 PORT HDJ, 10 WHITE
*S22HDJ10-99	SII 1U 2 PORT HDJ, 10 WM IVORY

*Note: Special Order – Lead time & minimum order quantities may apply, please contact sales support for details.

HDJ Jacks

HDJSN6	Clarity High Density Jack (HDJ) SNAP Cat6 Jack, T568 A/B
HDJSN6A	Clarity High Density Jack (HDJ) SNAP Cat6A Jack, T568 A/B
HDJHDMI	High Density Jack (HDJ) HDMI Coupler
HDJ35ST	Clarity High Density Jack (HDJ) Recessed 3.5mm Stereo (TRS) Jack To 3.5mm Stereo (TRS) Jack
HDJ6A	Clarity High Density Jack (HDJ) CAT6A, T568A/B
HDJS6A	Clarity Shielded High Density Jack (HDJS) CAT6A
HDJ21DCA	Clarity High Density Jack (HDJ) DC Barrel Plug Jack to Captive Screw Terminal

SII Jacks

60900378	Series II S-Video with 3.5mm
60900382	Series II, XLR, Screw Terminal
60900018	Series II, 1 BNC Connector F/F, 180 degree
60900380	Series II, Binding Post, Pair
60900020	Series II, 2 F Connectors F/F, 75 ohm, 180 degree, (1 GHz performance)
60900375	Series II, VGA, Screw Terminal
60900378	Series II, VGA, Feed-Thru
60900017	F Conn 75 ohm, female-to-female, 1-unit
60900372	Series II, HDMI, F/F, 180°, 1 Unit

