



Wiremold
Charging Station, 2-Gang, (1) Duplex GFCI, (1) Duplex GFCI with Dual USB-C - Bronze
Part No. XCSP2GRR1-BZ



Ideal for areas that are already illuminated, such as outdoor dining areas. Shorter height enables use besides tables or as a lower-profile solution in landscaping. Power Pedestal includes one duplex 20A, weather-resistant GFCI receptacle and one duplex 20A, weather-resistant GFCI Receptacle with USB-C.

Features & Benefits

Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.

Outdoor-Rated Construction: Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.

Durable, Premium Finishes: Available in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices.

Add up to two pairs of shelves to hold mobile devices while charging

Interior illuminates when door is open. Replace standard color-matched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

Available in several preconfigured options with various installed devices to meet exact charging needs.

Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

Specifications

General Info

| | | | |
|-----------------------|---|--------------------|-------------------|
| Product Line | Wiremold | Color | Bronze |
| UPC Number | 786776197617 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Features | USB-C Charging |
| Outlet Type | Weather-Resistant | Application Sector | Commercial |
| Standard | cULus Listed, File Number E479489, Guide PUPR | Type | Charging Stations |
| Installed Devices | GFCI with USB-C | | |

Dimensions

| | | | |
|---------------------------------------|----------|-------------------------------|---------|
| Product Width US | 6.0 in | Product Weight US | 35.0 lb |
| Product Height US | 34.0 in | Product Length US | 8.0 in |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | E479489 | cULus Listed | Yes |
| Additional Information | | | |
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
| Technical Information | | | |
| Is Pre-Wired | Yes | Number of USBs | 2 |
| Number of Gangs | 2 | Amperage | 20 A |
| Lighting Types | No Light | | |