

PASS & SEYMOUR®
PORTABLE GFCIs



ADDED SAFETY

ON THE JOB




designed to be better.™

 **legrand**®

HELPING CONTRACTORS AND FACILITY MANAGERS

KEEP IT SAFE

WITH CODE-COMPLIANT PORTABLE GFCI SOLUTIONS.



From the first in-wall GFCI receptacle to innovative portable solutions, we keep you safe on the job — anytime, anywhere.

In 1971, we introduced the first GFCI receptacle. Soon our innovation was preventing injuries and saving lives. That dedication to safety continues in our latest line of Portable GFCIs — a broad range of types that prevent injury from electrical shock by interrupting power in the event of a ground fault. These rugged devices provide a reliable solution for compliance with *National Electric Code*® (NEC) and OSHA requirements.

GFCI protection for any application.

P&S Portable GFCIs are perfect for a variety of temporary power applications, including use with power tools, high-pressure power washers, wet vacuums and grounds-keeping equipment, spas and hot tubs, vending machines, portable signs, and more.



Right-Angle Plug GFCI

Box Unit GFCI

- Handles up to four loads.
- Optional Turnlok® Plug and Connectors prevent accidental disconnection.
- 6' cord

In-Line Portable GFCI

- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional Tri-Cord connector handles up to three loads.

Adapter Plug GFCI

- Adapts any receptacle to provide GFCI protection.

Cord Set GFCI

= Bright, green power indicator light is on when power is available.

All P&S Portable GFCIs include these features:

- All models meet the latest requirements — UL GFCI standard, NEC®, and OSHA 1926.404 standards.
- Rugged polycarbonate housing stands up to impacts and hard use.
- Water-resistant design — In-Line, Cord Set, Right Angle, and Box GFCIs are rated for outdoor use.
- Automatic-reset models available for applications where continuous power is required (pumps, pressure washers, portable signs, lighting, and engine heaters).
- Watertight rubber cord grommets seal the GFCI from the environment (corded and in-line models).
- Open neutral protection, standard on all models, automatically cuts off power to the hot conductor if there's a loss in continuity in the neutral conductor leading to the device.
- Choose from 15A and 20A models to meet virtually any portable GFCI application requirement.



In-Line Portable Auto Reset GFCI

- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional Tri-Cord connector handles up to three loads.



1594ADPTM



1594CMM



1594PC2A



1594CS1M



PL204L

CATALOG NO.	DESCRIPTION	RESET	RATINGS		NEMA CONFIG. NO.	CONFIGURATION	
			A.	V.		PLUG	CONNECTION
ADAPTER PLUG — PORTABLE GFCI							
1594ADPTM	Outlet adapter	Manual	15	125	5-15P		
RIGHT ANGLE PLUG — PORTABLE GFCI							
1594CMM	User attachable	Manual	15	125	5-15P		N/A
1594CMA	User attachable	Automatic	15	125	5-15P		
15 AMP IN-LINE — PORTABLE GFCI							
1594PC6M	6' cord, straight blade	Manual	15	125	5-15P/R		
1594PC2M	2' cord, straight blade	Manual	15	125	5-15P/R		
1594PC2A	2' cord, straight blade	Automatic	15	125	5-15P/R		
1594TC2M	2' cord with tri-cord connector	Manual	15	125	5-15P/R		
1594TC2A	2' cord with tri-cord connector	Automatic	15	125	5-15P/R		
1594TL2M	2' cord, Turnlok®	Manual	15	125	L5-15P/R		
1594TL2A	2' cord, Turnlok	Automatic	15	125	L5-15P/R		
20 AMP IN-LINE — PORTABLE GFCI							
2094PC2A	2' cord, straight blade	Automatic	20	125	5-20P/R		
2094PC2M	2' cord, straight blade	Manual	20	125	5-20P/R		
2094TL2A	2' cord, Turnlok	Automatic	20	125	L5-20P/R		
2094TL2M	2' cord, Turnlok	Manual	20	125	L5-20P/R		
CORD SET — PORTABLE GFCI							
1594CS1M	1' cord with connector	Manual	15	125	5-15P/R		
1594CS1A	1' cord with connector	Automatic	15	125	5-15P/R		
BOX UNIT — PORTABLE GFCI							
PS154S	Four 15A, 125V straight blade outlets; cord has 15A, 125V plug	Automatic	15	125	5-15P 5-15R		
PS204S	Four 20A, 125V straight blade outlets; cord has 20A, 125V plug	Automatic	20	125	5-20P 5-20R		
PL204L	Two 20A, 125V straight blade outlets and one 20A, 125V locking outlet has 20A, 125V locking plug	Automatic	20	125	L5-20P L5-20R 5-20R		

All GFCIs are 3rd Party Compliant with UL943, UL498

designed to be better™

Legrand/Pass & Seymour

P.O. Box 4822
Syracuse, NY 13221-4822
800.776.4035
www.legrand.us/PassandSeymour



Legrand, North America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

Follow Us

