legrand®

Cablofil

FTX

HORIZONTAL CROSS BASE



FEATURES

- Strong corrosion resistant steel construction
- Rolled edge for cable protection
- Unique design allows covers to snap on
- 18 gage steel

COMPATIBLE COVER

FTXC

(sold separately)



	TRAY HEIGHT		TRAY WIDTH (W)		RADIUS (R)		LENGTH 1 (L1)		LENGTH 2 (L2)		TANGENT (C)		WEIGHT		PG	BL
	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	INCHES	MM	LBS	KG	STANDARD	
FTX 50/50	2.0	50	2.0	50	0.8	20	5.9	150	5.9	150	1.2	30	0.7	0,31	341 133	960 076
FTX 50/100	2.0	50	3.9	100	3.9	100	14.2	360	14.2	360	1.2	30	2.4	1,09	341 134	960 077
FTX 50/200	2.0	50	7.9	200	3.9	100	18.1	460	18.1	460	1.2	30	4.1	1,86	341 136	960 078
FTX 50/300	2.0	50	11.8	300	3.9	100	22.0	560	22.0	560	1.2	30	6.2	2,81	341 137	960 079
FTX 100/100	3.9	100	3.9	100	3.9	100	14.2	360	14.2	360	1.2	30	4.5	2,04	341 149	960 080
FTX 100/200	3.9	100	7.8	200	3.9	100	18.1	460	18.1	460	1.2	30	7.6	3,44	341 151	960 081
FTX 100/300	3.9	100	11.8	300	3.9	100	22.0	560	22.0	560	1.2	30	11.4	5,19	341 152	960 082
FTX 100/500	3.9	100	19.7	500	5.9	150	35.4	900	35.4	900	2.0	50	23.8	10,81	341 154	960 083
FTX 100/600	3.9	100	23.6	600	5.9	150	39.4	1000	39.4	1000	2.0	50	30.2	13,70	341 067	960 084

FINISHES			
SYMBOL		MATERIAL	FINISH & STANDARD
STANDARD	PG	Carbon Steel	**Pre-Galvanized:** Continuous Galvanization Before Fabrication ASTM A 653
	BL	Carbon Steel ASTM A510 Grade 1008	**Black Painted:** Black Powder Coated ASTM D 3451

© 2012 Legrand/Cablofil 02/12

Legrand/Cablofil
8319 State Route 4
Mascoutah, IL 62258 USA
1-800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil