

**Catalog Numbers • Les Numéros de Catalogue • Los Números de Catálogo:**

Country of Origin: Made in China • Pays d'origine: Fabriqué en Chine • País de origen: Hecho en China



**QIS WALL SWITCH PROGRAMMING INSTRUCTIONS****First Time Setup**

**IMPORTANT** – Read and understand each section before performing required steps. When using a Dual Channel Wall Switch, the left button column corresponds to Channel 1. The right button column corresponds to Channel 2 as shown in the diagram below.

1. INSTALL SHADE following appropriate installation instructions.
2. CONNECT POWER SUPPLY to Power Communication Panel.
3. CONNECT SHADE to Power Communication Panel using network cable.  
(Shade will JOG on initial power-up.)
4. CONNECT WALL SWITCH to Power Communication Panel using network cable.

**Pairing / Learning Wall Switch (or Channel)**

1. PRESS both UP and PRESET 1 at the same time.  
(Shade will JOG in response.)
2. TUG the HEMBAR 6-10 inches.  
(Shade will JOG in response and is now paired.)

**Single Channel Wall Switch****Dual Channel Wall Switch****Unpairing / Unlearning Wall Switch (or Channel)**


1. PRESS both DOWN and PRESET 2 at the same time.  
(Shade will JOG in response.)
2. TUG the HEMBAR 6-10 inches. (Shade will JOG in response and is now unpaired.)

**Setting Upper and Lower Limits**

You must use a paired wall switch to perform this task.

1. PRESS the UP or DOWN button that will be programmed. (Shade will move to selected position.)
2. PRESS and HOLD the same UP or DOWN button UNTIL shade JOGS.
3. TUG shade 6-10 inches. (Shade will JOG in response.)
4. ADJUST shade to desired position. (Use UP/DOWN buttons or manually adjust shade by hand.)
5. PRESS and HOLD the same UP or DOWN button. (Shade will JOG when learned.)

## QIS SYSTEM OVERVIEW



- Power Supply: 24 VDC, 7.5A
  - RJ-45 Ports for Motorized Shades and Switches - Quantity 8
  - Communication Ports (RJ-45) - Quantity 2
- CAT5e or CAT6 Cable Required for Network Connections (RJ-45)

### WARRANTY INFORMATION

#### Limited Lifetime Warranty

Legrand offers a Limited Lifetime Warranty for window shade product, and/or specific components of the window shade product to be free from defects in materials and workmanship under normal use. There are no obligations or liabilities on the part of Legrand for consequential damages arising out of, or in connection with, the use or performance of this product or other indirect damages with respect to loss of property, revenue or profit, or cost of removal, installation or reinstallation. For full warranty details visit <https://www.legrand.us/shading-warranty>

### INFORMATIONS RELATIVES À LA GARANTIE

#### Garantie à vie limitée

Legrand offre une garantie à vie limitée pour le produit de store de fenêtre et / ou des composants spécifiques du produit de store de fenêtre pour être exempt de défauts de matériaux et de fabrication dans des conditions normales d'utilisation. Il n'y a aucune obligation ou responsabilité de la part de Legrand pour les dommages consécutifs résultant de, ou en relation avec, l'utilisation ou la performance de ce produit ou d'autres dommages indirects en ce qui concerne la perte de propriété, de revenu ou de profit, ou le coût de l'enlèvement, installation ou réinstallation. Pour plus de détails sur la garantie, visitez <https://www.legrand.us/shading-warranty>

### INFORMACIÓN DE LA GARANTÍA

#### Garantía limitada de por vida

Legrand ofrece una garantía limitada de por vida para el producto de sombra de ventana, y / o componentes específicos del producto de sombra de ventana para estar libre de defectos en materiales y mano de obra bajo uso normal. No hay obligaciones ni responsabilidades por parte de Legrand por daños consecuentes que surjan de, o en conexión con, el uso o desempeño de este producto u otros daños indirectos con respecto a la pérdida de propiedad, ingresos o ganancias, o costo de remoción, instalación o reinstalación. Para obtener detalles completos de la garantía, visite <https://www.legrand.us/shading-warranty>