legrand®

Pass & Seymour

Weatherproof Boxes & Covers
Heavy Cast Aluminum Covers
Flush Enclosures

4600, 4600-1P, 4600-7P, 4600-8P, 4600-26P, 4609

Lock out weather — and unauthorized users.

These heavy aluminum covers keep weather out with neoprene gaskets — and unauthorized users out with a sturdy cam lock. Each cover comes with two keys. In addition to the mounting screws that secure covers to the box, these rugged covers lock into walls via mortar keys.



Features & Benefits

Adapter, frame and cover are heavy cast aluminum.

2 keys provided for cam lock.

Neoprene gasket seals cover to frame so moisture and dust cannot enter.

Mortar keys provide positive holding means within wall.

#8-32 screws hold assembly firmly in place.

4600

Field Uses/Vertical Markets

- Industrial
- Retail
- Health Care
- Office
- Education
- Hospitality/Lodging
- Institutional
- Multiple Dwelling

legrand®
Pass & Seymour

Weatherproof Boxes & Covers
Heavy Cast Aluminum Covers
Flush Enclosures

Ordering Information

Catalog Number	Description	Color
Mortared-in Applications		
4600	Enclosure Only, without Mounting Plate	Gray
4600-1P	Mounting Plate for Toggle Switch	Gray
4600-7P	Mounting Plate for Single Receptacle Diameter: 1.406"	Gray
4600-8P	Mounting Plate for Duplex Receptacle	Gray
4600-26P	Mounting Plate for Decorator/GFCI	Gray
4609	Key for Enclosure	—

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Weatherproof Boxes & Covers
Heavy Cast Aluminum Covers
Flush Enclosures

legrand®
Pass & Seymour

Technical Specifications

3rd Party Compliance

UL Listed.
CSA Certified.
Complies with 2002 NEC Section 406.8(A) and 406.8(B)(2).

Performance

Environmental	Corrosion-Resistant Weatherproof

Materials

Body	.125" Cast Aluminum
Springs	Stainless Steel
Hinges	Plated Steel Pins
Screws	Steel, Zinc-Plated or Aluminum
Gasket	Neoprene
Insert Plates	.086" Aluminum

Dimensions for Flush Enclosure

Warranty

1 Year

Complementary Devices & Accessories

WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Cast Covers
- Boxes

WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle

STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade

GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

legrand®

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF2302R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

© 2011, Legrand/Pass & Seymour GG/DG