A. Combination Tamper-Resistant Hospital-Grade Duplex Convenience Receptacles with (2) USB ports, 125 V, 20 A; overall 30W charging capability with (1) USB Type-A & (1) USB Type-C port powered by smart current sharing technology to allow for full 3A through a singular Type-C port.; slim design allows for installation in standard depth wall boxes; reinforced nylon USB Type-A ports; Stainless steel auto-ground clips assure positive ground; efficient power supply meets the US Department of Energy Level VI no-load power requirement of 100mW max for external power supplies. Comply with NEMA WD 1, NEMA WD 6 configuration 5-20R, UL 498 Supplement SD, UL 1310, CSA C22.2 No. 42, CSA 22.2 No. 223 and Federal Specification W-C-596.

1. Available Products: Subject to compliance with requirements, products that may be incorporated into the Work include, but are not limited to, the following:
2. Products: Subject to compliance with requirements, provide one of the following:

    a. Pass & Seymour; TR20HUSBAC6
    b. <**Insert manufacturer's name; catalog number.**>

3. Description: Labeled to comply with NFPA 70, "Health Care Facilities" Article, "Pediatric Locations" Section.

B. Combination Tamper-Resistant Specification Grade Duplex Convenience Receptacles with (2) USB ports, 125 V, 20 A; overall 30W charging capability with (1) USB Type-A & (1) USB Type-C port powered by smart current sharing technology to allow for full 3A through a singular Type-C port.; slim design allows for installation in standard depth wall boxes; reinforced nylon USB Type-A ports; Stainless steel auto-ground clips assure positive ground; efficient power supply meets the US Department of Energy Level VI no-load power requirement of 100mW max for external power supplies. Comply with NEMA WD 1, NEMA WD 6 configuration 5-20R, UL 498 Supplement SD, UL 1310, CSA C22.2 No. 42, CSA 22.2 No. 223 and Federal Specification W-C-596.

1. Available Products: Subject to compliance with requirements, products that may be incorporated into the Work include, but are not limited to, the following:
2. Products: Subject to compliance with requirements, provide one of the following:

    a. Pass & Seymour; TR20USBAC6
    b. <**Insert manufacturer's name; catalog number.**>

C. radiant® Combination Tamper-Resistant Residential Grade Duplex Convenience Receptacles with (2) USB ports, 125 V, 15A; overall 30W charging capability with (1) USB Type-A & (1) USB Type-C port powered by smart current sharing technology to allow for full 3A through a singular Type-C port.; slim design allows for installation in standard depth wall boxes; reinforced nylon USB Type-A ports; Stainless steel auto-ground clips assure positive ground; efficient power supply meets the US Department of Energy Level VI no-load power requirement of 100mW max for external power supplies. Comply with NEMA WD 1, NEMA WD 6 configuration 5-15R, CSA 22.2 No.42, CSA 22.2 No.223, UL 498, UL 1310.

1. Available Products: Subject to compliance with requirements, products that may be incorporated into the Work include, but are not limited to, the following:
2. Products: Subject to compliance with requirements, provide one of the following:

    a. Pass & Seymour; R26USBAC6
    b. <**Insert manufacturer's name; catalog number.**>

D. Combination Tamper-Resistant Hospital-Grade Duplex Convenience Receptacles with (2) USB ports, 125 V, 20 A; overall 30W charging capability with (2) USB Type-C port powered by smart current sharing technology to allow for full 3A through a singular Type-C port.; slim design allows for installation in standard depth wall boxes; Stainless steel auto-ground clips assure positive ground; efficient power supply meets the US Department of Energy Level VI no-load power requirement of 100mW max for external power supplies. Comply with NEMA WD 1, NEMA WD 6 configuration 5-20R, UL 498 Supplement SD, UL 1310, CSA C22.2 No. 42, CSA 22.2 No. 223 and Federal Specification W-C-596.

1. Available Products: Subject to compliance with requirements, products that may be incorporated into the Work include, but are not limited to, the following:
2. Products: Subject to compliance with requirements, provide one of the following:

    a. Pass & Seymour; TR20HUSBCC6
    b. <**Insert manufacturer's name; catalog number.**>

3. Description: Labeled to comply with NFPA 70, "Health Care Facilities" Article, "Pediatric Locations" Section.

E. Combination Tamper-Resistant Specification Grade Duplex Convenience Receptacles with (2) USB ports, 125 V, 20 A; overall 30W charging capability with (2) USB Type-C port powered by smart current sharing technology to allow for full 3A through a singular Type-C port.; slim design allows for installation in standard depth wall boxes; Stainless steel auto-ground clips assure positive ground; efficient power supply meets the US Department of Energy Level VI no-load power requirement of 100mW max for external power supplies. Comply with NEMA WD 1, NEMA WD 6 configuration 5-20R, UL 498 Supplement SD, UL 1310, CSA C22.2 No. 42, CSA 22.2 No. 223 and Federal Specification W-C-596.

1. Available Products: Subject to compliance with requirements, products that may be incorporated into the Work include, but are not limited to, the following:
2. Products: Subject to compliance with requirements, provide one of the following:

    a. Pass & Seymour; TR20USBCC6
    b. <**Insert manufacturer's name; catalog number.**>

F. radiant® Combination Tamper-Resistant Residential Grade Duplex Convenience Receptacles with (2) USB ports, 125 V, 15A; overall 30W charging capability with (2) USB Type-C port powered by smart current sharing technology to allow for full 3A through a singular Type-C port.; slim design allows for installation in standard depth wall boxes; stainless steel auto-ground clips assure positive ground; efficient power supply meets the US Department of Energy Level VI no-load power requirement of 100mW max for external power supplies. Comply with NEMA WD 1, NEMA WD 6 configuration 5-15R, CSA 22.2 No.42, CSA 22.2 No.223, UL 498, UL 1310.

1. Available Products: Subject to compliance with requirements, products that may be incorporated into the Work include, but are not limited to, the following:
2. Products: Subject to compliance with requirements, provide one of the following:

    a. Pass & Seymour; R26USBCC6W
    b. <**Insert manufacturer's name; catalog number.**>