SWM Series Swing-Out Wall-Mount Cabinet - 18RU

Models:
SWM18RUSD-26-26
SWM18RUPL-26-26
SWM18RUPD-26-26

A. Reversible Solid Front Door*
B. Reversible Plexiglass Front Door*
C. Reversible Perforated Front Door*
D. Locking Swing Handle
E. Reversible Backpan
F. Back Panel Lock
G. Mounting Rails
H. Wire Management Rings
I. Vented Cooling Area
J. Cable Conduit Knockouts

* Only 1 door type is supplied with each cabinet.
Please refer to model numbers below for door type.



Cabinet Includes:

(2) Adjustable Rails (partially shown)
(1) Backpan Bonding Wire
(1) Door Bonding Wire
(2) Keys with Door Lock
(2) Keys with Backpan Lock
(8) Wire Management Rings
(1) Owner's Manual
Includes Associated Hardware

Legrand offers a 5 year warranty on all Swing-Out Wall-Mount Cabinets.

The Legrand SWM Series has a full line of accessories to enhance network cable management. See data sheet for details.

Specifications

Models	SWM18RUSD-26-26	SWM18RUPL-26-26	SWM18RUPD-26-26
Door Type	Solid Front Door	Plexiglass Front Door	Perforated Front Door
Rack Units	18RU	18RU	18RU
Equipment Mounting Depth	23.5 in	23.5 in	23.5 in
UL 2416 Certified Load Rating**	275 lbs	275 lbs	275 lbs
Unit Dimensions H x W x D	35.4 x 26 x 28 in	35.4 x 26 x 28 in	35.4 x 26 x 28 in
Shipping Dimensions H x W x D	41 x 29.5 x 30.5 in	41 x 29.5 x 30.5 in	41 x 29.5 x 30.5 in
Unit Weight	114 lbs	114 lbs	114 lbs
Shipping Weight	135 lbs	135 lbs	135 lbs
Certifications/Compliances	TAA Compliant, UL2416 Certified, PCI Compliant, EIA-310-E Compliant, RoHS Complaint, Product Environmental Profile (PEP) Compliant		

** These cabinets are load rated to 275lbs per UL2416 certification. This rating is in addition to the weight of the unit and is certified at a single set of rails.

SWM Series Swing-Out Wall-Mount Cabinet

SWM18RUSD-26-26 - 18RU Swing-Out Wall-Mount Cabinet with Solid Door - 26in
SWM18RUPL-26-26 - 18RU Swing-Out Wall-Mount Cabinet with Plexiglass Door - 26in
SWM18RUPD-26-26 - 18RU Swing-Out Wall-Mount Cabinet with Perforated Door - 26in

Dimensions: INCHES



REAR OPENING



TOP VIEW

FRONT OPENING



TOP/BOTTOM VIEW



CROSS SECTION A
USABLE MOUNTING DEPTH



FRONT VIEW



REAR VIEW



SIDE VIEW