Nuvo®

Landscape Speakers

Deliver immersive sound throughout any outdoor environment with the durable and scalable Nuvo Series Two Landscape Speaker Kit, complete with four, two-way satellite speakers and an eight inch, in-ground subwoofer. The low-profile, black teardrop satellite speakers have 3.5" poly woofers and .5" UFLC tweeters for clear, robust audio and even coverage. The powerful, eight inch subwoofer's cylindrical enclosure blends subtly into landscaping while providing stand-out bass response.

- **Complete 5-piece system delivers immersive sound in outdoor environments**
- **IP-67 and MIL-STD-810 compliant to provide years of reliable performance in harsh weather conditions.**
- **8 ohm system pairs perfectly with Nuvo Player amplifiers or can be used with any 8 ohm amplifier**
- **Easy to expand for larger areas with additional satellite speakers (NV-2LS3-SAT2)**
- **LIfetime warranty**

legrand®

Nuvo® NV-2LSK-BK Landscape Speaker Kit

SATELLITE SPEAKERS SPECIFICATIONS

Materials

ABS Plastic, Aluminium, Poly Propelene

Output

Speaker Impedance

16 Ohms per satellite

4 satellites and 1 subwoofer	8 Ohms
6 satellites and 1 subwoofer	6 Ohms
8 satellites and 1 subwoofer	4 Ohms

Power Handling: 20 watts RMS, 40 watts Peak

Efficiency: 83 dB

Regulatory Approvals

Safety: RoHS Restriction of Hazardous Substances Directive 2002/95/EC, Reach, IP-67, MIL-STD-810

Weight

Unit Weight (kg): 2.4 kg
Unit Weight (lbs): 5.29 lbs

Shipping Weight (kg): 3.8 kg
Shipping Weight (lbs): 8.38 lbs

Unit Size

Unit Size (mm): 432.21 L x 184.73 W x 137.84 H
Unit Size (inch): 17.02 L x 5.43 W x 8.03 H

Shipping Specifications

Unit Size (mm): 310 L x 240 W x 380 H
Unit Size (inch): 12.2 L x 9.4 W x 15 H

Legrand reserves the right to change specifications without notice.

SUBWOOFER SPECIFICATIONS

Materials

ABS Plastic, Aluminium, Poly Propelene

Output

Speaker Impedance

6 Ohms - Subwoofer only

4 satellites and 1 subwoofer	8 Ohms
6 satellites and 1 subwoofer	6 Ohms
8 satellites and 1 subwoofer	4 Ohms

Power Handling: 200 watts RMS (100 watts per channel), 400 watts Peak (200 watts per channel)

Efficiency: 87 dB

Regulatory Approvals

Safety: RoHS Restriction of Hazardous Substances Directive 2002/95/EC, Reach, IP-67, MIL-STD-810

Unit Size

Unit Size (mm): 527.98 L x 265 W x 265 H
Unit Size (inch): 20.78 L x 10.4 W x 10.4 H

Shipping Specifications

Shipping Size (mm): 338 L x 540 W x 725 H
Shipping Size (inch): 13.3 L x 21.25 W x 28.5 H

Legrand reserves the right to change specifications without notice.

Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo