WWW.LEGRAND.US

TITLE:

Q-SERIES OVERHEAD RACK SYSTEM ASSEMBLY INSTRUCTIONS



NOTES

1. MAXIMUM MOUNTED PATCH PANEL LOAD SHALL NOT EXCEED 50 LBS.
2. SEE SHEET 2 FOR MOUNTING OPTIONS TO CABLE TRAYS.

INSTRUCTION SHEET #:	REV:	ECN #:	SHEET:	DWN BY:	DATE:	CHK BY:	DATE:	APP. BY:	DATE:
OR-71601927	00		1 of 2	JS	2/10/2017	JQ	2/10/2017	CV	2/15/2017

WWW.LEGRAND.US

TITLE:

Q-SERIES OVERHEAD RACK SYSTEM ASSEMBLY INSTRUCTIONS

STEP 1

DETERMINE IF THE MOUNTING EQUIPMENT WILL MOUNT TO EITHER A CABLE TRAY OR CEILING MOUNT (THREADED RODS OR HANGERS NOT SUPPLIED).



CABLE TRAY BRACKET

STEP 2

DETERMINE THE MOUNTING POSITION OF THE UNIT. THE MOUNTING OPTIONS ARE: REAR TOP, REAR MIDDLE, REAR BOTTOM, UNDERNEATH PARALLEL, UNDERNEATH PERPENDICULAR.



CABLE TRAY
TOP MOUNTING



CABLE TRAY
MIDDLE MOUNTING



CABLE TRAY
BOTTOM MOUNTING



UNDERNEATH PARALLEL



UNDERNEATH PERPENDICULAR

INSTRUCTION SHEET #:	REV:	ECN #:	SHEET:	DWN BY:	DATE:	CHK BY:	DATE:	APP. BY:	DATE:
OR-71601927	00		2 of 3	JPS		JQ	2/10/2017	CV	2/15/2017

WWW.LEGRAND.US

TITLE:

Q-SERIES OVERHEAD RACK SYSTEM ASSEMBLY INSTRUCTIONS

STEP 3

ONCE THE MOUNTING LOCATION IS DETERMINED, MOUNT 2 CABLE TRAY BRACKETS USING (8) SPLIT LOCK WASHERS AND (8) PAN HEAD SCREWS.



CABLE TRAY BRACKETS

STEP 4

HANG ASSEMBLY ONTO CABLE TRAY WHERE REQUIRED.



INSTALLATION IS NOW COMPLETE.

INSTRUCTION SHEET #:	REV:	ECN #:	SHEET:	DWN BY:	DATE:	CHK BY:	DATE:	APP. BY:	DATE:
OR-71601927	00		3 of 3	JPS		JQ	2/10/2017	CV	2/15/2017