



HDJ Angled Faceplate

Description

HDJ faceplates made from durable thermoplastic. Angled to allow for optimal bend radius. Available in a variety of colors to match your workstation applications. For more information, please contact your local sales representative.

Features & Benefits

- Angled for easy access to jack
- Angled for optimized bend radius
- Compatible with old or new work boxes
- Recessed jack allows for extra room behind plate
- Angled design protects jack from furniture or other outside forces contacting it
- Ec0-friendly mounting screw attached which eliminates a single-use plastic bag

Color	Fog White, Black, Ivory, WM Dark Gray, White, WM Ivory
Country of Origin	Taiwan
Type	Keystone
Standard	UL 1863

Dimensions

Product Width	4 in
Product Height	1 in
Product Depth	1 in

Technical Information

Construction	Plastic
Use Type	HDJ Angled Faceplate
Compatibility	568A/B
Ports	2, 4
Contact Resistance	<20mOhms
Insertion Loss	<0.45dB@500Mhz
Withstand Voltage	1000 VAC
Operating Temp	-20° - 85° C

Ordering Information

403HDJA12	ANG FP, HDJ, 1 GANG, 2P, FOG WHITE
403HDJA12-00	ANG FP, HDJ, 1 GANG, 2P, BLACK
403HDJA12-13	ANG FP, HDJ, 1 GANG, 2P, IVORY
403HDJA12-78	ANG FP, HDJ, 1 GANG, 2P, WM DK GRAY
403HDJA12-88	ANG FP, HDJ, 1 GANG, 2P, WHITE
403HDJA12-99	ANG FP, HDJ, 1 GANG, 2P, WM IVORY
403HDJA14	ANG FP, HDJ, 1 GANG, 4P, FOG WHITE
403HDJA14-00	ANG FP, HDJ, 1 GANG, 4P, BLACK
403HDJA14-13	ANG FP, HDJ, 1 GANG, 4P, IVORY
403HDJA14-78	ANG FP, HDJ, 1 GANG, 4P, WM DK GRAY
403HDJA14-88	ANG FP, HDJ, 1 GANG, 4P, WHITE
403HDJA14-99	ANG FP, HDJ, 1 GANG, 4P, WM IVORY

*Note: Special Order –Lead time & minimum order quantities may apply, please contact sales support for details.

HDJ Jacks

HDJSN6	Clarity High Density Jack (HDJ) SNAP Cat6 Jack, T568 A/B
HDJSN6A	Clarity High Density Jack (HDJ) SNAP Cat6A Jack, T568 A/B
HDJHDMI	High Density Jack (HDJ) HDMI Coupler
HDJ35ST	Clarity High Density Jack (HDJ) Recessed 3.5mm Stereo (TRS) Jack To 3.5mm Stereo (TRS) Jack
HDJ6A	Clarity High Density Jack (HDJ) CAT6A, T568A/B
HDJS6A	Clarity Shielded High Density Jack (HDJS) CAT6A
HDJ21DCA	Clarity High Density Jack (HDJ) DC Barrel Plug Jack to Captive Screw Terminal

