NOTES:
1. THE "CCC" SUFFIX IN THE PART NUMBER INDICATES THE CORE SIZE AND THE GRADE OF THE PRE-POLISHED FIBER STUB IN THE CONNECTOR BODY, SEE TABLE 1.
2. CONNECTOR (ITEM 1) SHALL BE PER TABLE 1.
3. CONNECTORS SHALL BE INDIVIDUALLY BAGGED USING (ITEM 2).
4. PACK INDIVIDUAL CARTON WITH 12 CONNECTOR KITS, AS DESCRIBED ABOVE, INCLUDE KIT OF PROTECTIVE TUBES (ITEM 3), 1 FIBER HOLDER (ITEM 4), 1 ASSEMBLY JIG (ITEM 5), AND 1 INSTRUCTION SHEET (ITEM 10). APPLY SMALL BAR CODE (ITEM 7), QR CODE (ITEM 6), AND TAMPER EVIDENT LABEL (ITEM 9).
5. QR CODE LABEL (ITEM 6), IDENTIFIED AS PRODUCT INFORMATION, SHALL BE AFFIXED ADJACENT TO (ITEM 7).
6. PACK INNER CARTON WITH 10 INDIVIDUAL CARTONS, AS DESCRIBED ABOVE. APPLY BAR CODE (ITEM 8) AND TAMPER EVIDENT LABEL (ITEM 9).
7. PACK MASTER CARTON WITH 6 INNER CARTONS. APPLY BAR CODE (ITEM 8) AND TAMPER EVIDENT LABEL (ITEM 9).
8. APPLY TAMPER EVIDENT LABEL TO CENTER OF OPENING ON INDIVIDUAL, INNER & MASTER CARTONS.
9. PACKAGING AND ENVIRONMENTAL COMPLIANCE SHALL BE IN ACCORDANCE WITH OR-71700217.

REVISIONS						
ECN#	ZONE	REV	DESCRIPTION	REV BY	CHK BY	DATE
		00	INITIAL RELEASE	NR	RJG	04/14/14
04658		01	UPDATE QR CODE LINK	RJG	NR	06/10/14
04693		02	ADDED 62.5 CONNECTOR SUPPORT	RJG	JL	10/14/14
05840		03	ITEM 10 WAS UPDATED	KV	JL	9/26/25



OR–205KNT9YA–CCC

BASE NUMBER

POLISH (SEE TABLE 1)

CORE TYPE (SEE TABLE 1)

PART NUMBER LEGEND

TABLE 1				
-"G"	-"CCC"	CORE/CLAD (µm)	ITEM 1	STANDARD COLOR
S	09	9/125	951-191-111	BLUE
G	50T	50/125	951-491-511	AQUA
G	62	62.5/125	951-391-211	BEIGE



QR CODE LABEL FORMAT

QR CODE FOR: OR-205KNT9SA-09

QR CODE FOR: OR-205KNT9GA-62

QR CODE FOR: OR-205KNT9GA-50T

ITEM	QUAN	PART NUMBER	SUPPLIER/VENDOR	DESCRIPTION
13	0.0014			CARTON, MASTER, KRAFT, 10.5 X 17.3 X 20.5 OR EQUIV
12	0.0083			CARTON, INNER, KRAFT, 6 X 8.3 X 9.6 OR EQUIV
11	0.0833			CARTON, INDIVIDUAL, KRAFT, 1.5 X 4.5 X 5.3 OR EQUIV
03 10	0.0833	OR-71601852		INSTRUCTION SHEET, FIELD TERM, FIBER CONNECTOR, LC
9	0.093	OR-70400844		LABEL, TAMPER EVIDENT, 3 X 2
8	0.0097	OR-70400731		LABEL, BAR CODE, THERMAL, 4 X 2
7	0.0833	OR-70400665		BLANK, LABEL, WHITE THERMAL, 1.75 X 1.25
6	0.0833	OR-70400067		BLANK LABEL, WHITE THERMAL, .625 X 1.5
5	0.0833		SENKO	JIG, ASSEMBLY
4	0.0833		SENKO	HOLDER, FIBER
3	0.0833		SENKO	TUBES, PROTECTIVE, 12 PACK
2	1			BAG, POLYETHYLENE, 3 X 5.5, 3 MIL, HEAT SEAL, TEAR OPEN (OR EQULIV)
1	1	SEE TABLE 1	SENKO	CONN, LC 900µm. PRE-POLISHED STUB, REUSABLE

UNLESS OTHERWISE STATED:
DIMENSIONS ARE IN INCHES

TOLERANCES:
FRACTIONAL ±
ANGULAR: MACH ± 1° BEND ± 1°
ONE PLACE DECIMAL ±
TWO PLACE DECIMAL ± .020
THREE PLACE DECIMAL ± .010

MATERIAL
SEE INDIVIDUAL COMPONENTS

FINISH
SEE INDIVIDUAL COMPONENTS

*** NOTICE ***
THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF ORTRONICS, INC.

	NAME	DATE
DWN	NR	02/27/2014
CHK	RJG	2/28/2014
APPR	RAM	2/28/2014

ORTRONICS®
125 EUGENE O'NEILL DRIVE
NEW LONDON, CT 06320
TEL: 860–445–3800
FAX: 860–405–2990
WWW.ORTRONICS.COM

TITLE

KIT, CONN, LC, 1 PC, FIELD INSTALL, REUSABLE, 900µm

SIZE	CAD FILE	DWG NO	REV
B	205KNT9YACCC1	OR-205KNT9YA-CCC	03

SCALE 2:1 SHEET 1 OF 1