


EZ PATCH™ FLAT PACK

REDUCED DIAMETER PATCH CORDS



EZ Patch Flat Packs deliver bulk packaged cords in patch panel quantities, offering 12 cords to be quickly and efficiently distributed from flat plastic packaging, ideal for patch panel applications. Reduced Diameter Cords are ideal for high density applications. The smaller cable surface area enables increased passive airflow and a smaller bend radius, so that cords are easily routed through cable management accessories.

EZ Patch Flat Packs are bagged with patch cords straight and flat, offering a quick and convenient way to introduce new cabling to a data network. Flat Packs offer a cleaner, dust free application when cardboard is not permitted in the data center. Cord memory is no longer an issue, meaning the cords are ready to install neatly in a bundle, without any kinks or curves. Perforation tear strips on both ends, provides quick connectivity options and improves cable management during installation. Overall, the Flat Pack means faster installation, less packaging waste and no more zip or twist ties.

FEATURES:

- ✓ **Reduced Diameter:** 28 AWG is ideal for high density applications, providing better flexibility, higher densities and promotes passive airflow for side breating equipment.
- ✓ **Bulk Packaging:** Reduces installation time and packaging waste. No dealing with individual bags or zip ties.
- ✓ **No cord memory:** Packs are laid out flat in a bundle. Cords are ready to install in a clean bundle without any bends or kinks from packaging.
- ✓ **Plastic packaging:** Ideal for data center applications that do not allow cardboard.
- ✓ **Light weight design:** Installers can easily carry the bag over their shoulder.
- ✓ **Easy tear perforation strips:** Tears at each end allow for quick connection and easy removal of cords.
- ✓ **Cable management:** Bag can be used as a fishing mechanism to route a bundle through a vertical manager.

EZ PATCH™ FLAT PACK REDUCED DIAMETER PATCH CORDS

REDUCED DIAMETER CAT6:

Part Number	Description	QTY Per Bag
EZFPR603Q12-XX	3ft EZ Patch™ Flat Pack Reduced Diameter CAT6 Cord	12
EZFPR605Q12-XX	5ft EZ Patch™ Flat Pack Reduced Diameter CAT6 Cord	12
EZFPR607Q12-XX	7ft EZ Patch™ Flat Pack Reduced Diameter CAT6 Cord	12
EZFPR609Q12-XX	9ft EZ Patch™ Flat Pack Reduced Diameter CAT6 Cord	12

Note: To order standard colors, replace XX suffix: -00 = Black, -06 = Blue, -08 = Gray, -09 = White

REDUCED DIAMETER CAT6A:

Part Number	Description	QTY Per Bag
EZFPR6A03Q12-XX	3ft EZ Patch™ Flat Pack Reduced Diameter CAT6A Cord	12
EZFPR6A05Q12-XX	5ft EZ Patch™ Flat Pack Reduced Diameter CAT6A Cord	12
EZFPR6A07Q12-XX	7ft EZ Patch™ Flat Pack Reduced Diameter CAT6A Cord	12
EZFPR6A09Q12-XX	9ft EZ Patch™ Flat Pack Reduced Diameter CAT6A Cord	12

Note: To order standard colors, replace XX suffix: -00 = Black, -06 = Blue, -08 = Gray, -09 = White



EZFPR603Q12-06

SPECIFICATIONS:

- ✓ **Cable Types:** Cat 6 & Cat6a
- ✓ **Connector Type End One:** RJ45
- ✓ **Connector Type End Two:** RJ45
- ✓ **Pair Count:** 4
- ✓ **Cat6 Wire Gauge:** 28 AWG
- ✓ **Cat6a Wire Gauge:** 28 AWG
- ✓ **Performance Categories:** Cat6 & Cat6a component compliant
- ✓ **Product Series:** Reduced Diameter
- ✓ **Type:** Patch Cords and Cables
- ✓ **Installation Destination:** Data Centers, Telecom Rooms, and Building Networks

LISTING AGENCIES/

THIRD PARTY CERTIFICATIONS:

- ✓ **RoHS:** Yes

TECHNICAL INFORMATION:

- ✓ **Category Ratings:** Cat6 & Cat6a component compliant
- ✓ **Performance Ratings:** Cat6 & Cat6a

BUY AMERICAN ACT COMPLIANCE:

- ✓ **Buy American Act Status:** Trade Agreement Act Compliant