

Turnlok® Single Receptacle 3-Wire 15A 125A



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                   |                |          |        |
|-------------------|----------------|----------|--------|
| Product Line      | Pass & Seymour | Color    | Black  |
| Country Of Origin | Mexico         | Standard | UL 498 |

### Dimensions

|                   |          |                  |        |
|-------------------|----------|------------------|--------|
| Product Width US  | 1.437 in | Product Depth US | 1.0 in |
| Product Height US | 2.25 in  |                  |        |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

## Additional Information

---

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

---

## Technical Information

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 15 A |
|-----------------|---|----------|------|

---

|                 |             |           |   |
|-----------------|-------------|-----------|---|
| Number of Poles | Double Pole | Wire Size | 4 |
|-----------------|-------------|-----------|---|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---