



adorne Collection
adorne® 15A One-Gang Pop-Out Outlet, White
Part No. ARPTR151GW2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 3-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Provides additional power with 3-plug access when extended from wall.

Disappears back into the wall with a simple push when not needed.

Installs easily in as little as 15 minutes.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Finish	Matte
Country Of Origin	China	Number of Receptacles	3
Features	Pop-Out	Outlet Type	Indoor, Pop-Out, Residential, Tamper-Resistant
Application Sector	Residential	Standard	CULUS
Warranty Type	Limited Lifetime Warranty	Type	Outlet

Dimensions

Product Width US	2.99 in	Product Depth US	2.6 in
------------------	---------	------------------	--------

Product Height US	4.88 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Connection	Side and Back Wire
-------	--------	------------	--------------------

Number of Wires	3	Number of Gangs	1
-----------------	---	-----------------	---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

NEMA Configuration Code	5-15R	Mounting Type	Box
-------------------------	-------	---------------	-----

Voltage	125.0 V	Connection Type	Internal Pressure Plates
---------	---------	-----------------	--------------------------

Environmental Conditions	95% (relative humidity, non-condensing)
--------------------------	---
