



adorne Collection
adorne® Dual-USB Outlet, Graphite
Part No. ARTRUSB153G4



Get a full battery for your phones, tablets and more with the convenience of built-in charging. Including two USB Type-A connections and replacing a traditional outlet in as little as ten minutes, this adorne USB Outlet provides easy-to-access charging without sacrificing a plug or finding that bulky adapter. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Features a total charging capacity of 3.1A.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Replaces a traditional outlet easily, in as little as 10 minutes.

Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Graphite	Country Of Origin	China
Number of Receptacles	2	Features	USB-A Charging
Outlet Type	Indoor, Residential, Tamper-Resistant, USB-Charging	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

Dimensions

Product Width US	1.77 in	Product Depth US	1.48 in
------------------	---------	------------------	---------

Product Height US 2.65 in

Technical Information

USB Amperage 3.1 A Connection Side and Back Wire

Number of USBs 2 Number of Gangs 1

USB Power Output 15 W Amperage 15 A

Number of Poles Double Pole Indoor/Outdoor Indoor

NEMA Configuration Code 5-15R Mounting Type Box

Voltage 125.0 V Connection Type Internal Pressure Plates

Environmental Conditions 95% (relative humidity, non-condensing)
