



Wattstopper
Dual Tech Occupancy Sensor, 24VDC, center mount 360°, 40 Khz
Part No. DT-305



The DT-300 Series Dual Technology Ceiling Sensors combine the benefits of passive infrared (PIR) and ultrasonic technologies to detect occupancy. Sensors have a flat, unobtrusive appearance and provide 360 degrees of coverage.

Features & Benefits

Sensors work with low-voltage momentary switches to provide manual control

LEDs indicate occupancy detection

Eight occupancy logic options provide the ability to customize

BAA/TAA-compliant models available

Patented ultrasonic diffusion technology spreads coverage to a wider area

Uses plug terminal wiring system for quick and easy

Available with isolated relay for integration with BAS or HVAC

Specifications

General Info

| | | | |
|--------------------|-------------|---------------|--|
| Product Line | Wattstopper | UPC Number | 754182913831 |
| Country Of Origin | China | Features | Indicator Lights, IR (Infrared), Motion Sensor |
| Application Sector | Commercial | Warranty Type | 5-Year |

Dimensions

| | | | |
|-------------------|------------|-------------------|---------|
| Product Width US | 4.0 in | Product Weight US | 0.58 lb |
| Product Volume US | 47.5 cu in | Product Depth US | 5.0 in |
| Product Height US | 2.0 in | | |

Additional Information

| | | | |
|-----------------|-----|--|-----|
| RoHS Conformant | Yes | DesignLights Consortium Qualified System | Yes |
|-----------------|-----|--|-----|

| | | | |
|----------|-----|-------------------------------|-----|
| Security | Yes | Product Environmental Profile | Yes |
|----------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-------------|-----------|----------|------|
| Sensor Type | Occupancy | Amperage | 35 A |
|-------------|-----------|----------|------|

| | | | |
|-----------|-----------|---------------|-------------------------|
| Indicator | LED Light | Sensing Range | 1000 sq ft, 360 degrees |
|-----------|-----------|---------------|-------------------------|

| | | | |
|---------|--------|-----------------|-------|
| Voltage | 24.0 V | Connection Type | Wired |
|---------|--------|-----------------|-------|
