



Wattstopper High/Low PIR Fixture Sensor Low Voltage, 12-32VDC Part No. FSP-201B



The FSP-2x1B sensors provide multi-level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via a wireless configuration tool capable of storing and transmitting sensor profiles. The FSP-2x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

Features & Benefits

| | |
|---|---|
| Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting | Fully adjustable high and low dimmed light levels |
| Hold off setpoint with automatic calibration option for convenience and added energy savings | Adjustable via handheld wireless configuration tool |
| IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40' | Adjustable time delay and cutoff delay |

Specifications

General Info

| | | | |
|--------------|--------------|-------------------|-------|
| Product Line | Wattstopper | Color | White |
| UPC Number | 754182939466 | Country Of Origin | China |

Dimensions

| | | | |
|-------------------|-------------|-------------------|---------|
| Product Width US | 4.0 in | Product Weight US | 0.31 lb |
| Product Volume US | 21.94 cu in | Product Depth US | 2.31 in |
| Product Height US | 2.3 in | | |

Additional Information

| | | | |
|-----------------|-----|--|-----|
| RoHS Conformant | Yes | DesignLights Consortium Qualified System | Yes |
|-----------------|-----|--|-----|

Security

Yes

Product Environmental Profile

Yes

Technical Information

Sensor Type

Daylight, Occupancy
