



**Pass and Seymour**  
**30A 3 Pole 4 Wire Fusible Mechanical Interlock**  
Part No. PS430FMIR7W



Three pole, Four wire, Fusible Mechanical Interlock Receptacle, 30 amp, 3/480 vac.

## Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	United States	Application Sector	Industrial
Standard	UL Listed		

### Dimensions

Product Width US	9.13 in	Product Depth US	8.25 in
Product Height US	11.5 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

---

Phase	Three	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Voltage	480.0 V		

---