



**Wiremold**  
**Wiremold 20GB606 Plugmold Multioutlet System in Ivory**  
 Part No. V20GB606



The Wiremold 2000 Series raceway offers a selection of steel, aluminum, and nonmetallic raceways that provide a versatile solution for many applications. Plugmold sections offer single or alternating circuits, in standard or isolated ground receptacles. The ScuffCoat finish is scratch resistant and protects against nicks and chips while preventing color from fading.

## Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

## Specifications

### General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776093254	Country Of Origin	United States
Number of Receptacles	12	Application Sector	Residential/Commercial
Standard	cULus Listed Multioutlet Assembly: File E15191 Guide PVGT/PVGT7	Type	Plugmold

---

## Dimensions

---

Product Width US	72.0 in	Product Weight US	3.4 lb
Product Volume US	79.2 cu in	Product Depth US	0.88 in
Product Height US	1.25 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

## Additional Information

---

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

## Technical Information

---

Frequency Rating	60 Hz	Amperage	15 A
Enclosure Type	Steel	Voltage	125.0 V
Environmental Conditions	Dry interior locations		

---