



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 125V



Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

UV-resistant nylon face for longer life under adverse environmental conditions.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	United States	Application Sector	Commercial

WR marking on face as required by UL Standard.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Internal screw-pressure-plate back and side wire capability.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Standard	UL498, CSA C22.2 No. 42
----------	-------------------------

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Voltage	125.0 V
-----------	-------------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------
