

radiant Collection radiant® Tamper-Resistant Weather-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Gray Part No. 1597TRWRGRY



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen - no more confusion at the breaker box. Also including tamper and weather resistance, this model was designed for use on decks, patios, pool areas, and other outdoor spaces. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

current hardware and lighting trends.

## Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike Conducts an industry-leading automatic self-test every 3 seconds. If the breaker alternatives, GFCI receptacles make it easier to fix trips with a device ever fails, the indicator light flashes to signal it should be reset button right on the device. replaced. Extends GFCI protection to "downstream" outlets when used with feed-Equipped with proven SafeLock protection feature: if critical components thru wiring configuration. Note: Will cut power to face and downstream are damaged and protection is lost, power to the outlet is disconnected. outlets if wired incorrectly.

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. \*Must be installed in weatherproof enclosure per NEC requirements.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

1.73 in

## **Specifications**

## General Info

Color

Type

Product Line Pass & Seymour Replaced by Part Number Finish Gray Matte Country Of Origin Number of Receptacles 2 China GFCI, Outdoor, Residential, Self-Test, Outlet Type Application Sector Residential/Commercial Weather-Resistant Standard cULus, UL Listed, FSUL 1-Year Limited Warranty Warranty Type Outlet Dimensions

Product Width US

Product Depth US

1.13 in

Replaces any standard receptacle with ease, in as little as 10 minutes.

More color options available to fit any style, including finishes to match

Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Indoor/Outdoor	Outdoor	NEMA Configuration Code	5-15R
Mounting Type	Box	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		