

Pass and Seymour Heavy Duty Spec Grade Single Receptacles, Back and Side Wire, 15A, 250V, Ivory Part No. 5671I



Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 250V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy splitcircuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Temperature Rise: Maximum 30°C temperature rise at full-rated current

Specifications

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click

General Info

Product Line	Pass & Seymour	Color	lvory
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in		
Product Height US	1.68 in				
Listing Agencies / 3rd Party Agencies					
cUL ListingNumber	140596	cULus Listed	Yes		
cUL Listed	Yes				
Technical Information					
Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire		
Number of Wires	3	Temperature Rating	-40° - 60° C		
Amperage	15 A	Number of Poles	Double Pole		
Wire Size	14 - 10 AWG	Voltage	250.0 V		
Environmental Conditions	Flammability: UL94 V2				