



## Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back and Side Wire 15A 125V



### Features & Benefits

Impact-resistant nylon face.

One-piece heat-treated triple-wipe brass power contacts.

Easily accessible break-off line contact connecting tab for split circuit wiring.

Corrosion-resistant, zinc-plated steel strap is locked in.

Internal screw-pressure-plate back wire and side wire line terminals accept #14 : #10 AWG copper or copper-clad conductors.

High strength thermoplastic back body.

Auto-ground clip assures positive ground.

Compact design for easy installation.

Tri-drive terminal and mounting screws.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

#### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

---

Product Height US      3.281 in

---

**Listing Agencies / 3rd Party Agencies**

---

cULus ListingNumber      140596      cULus Listed      Yes

---

**Technical Information**

---

Dielectric Strength      Withstands 2000V minimum      Temperature Rating      -40° - 60° C

---

Amperage      15 A      Number of Poles      Double Pole

---

Wire Size      14 - 10 AWG      Indoor/Outdoor      Indoor

---

Voltage      125.0 V

---