



Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V



## Features & Benefits

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

LED Indication: Steady green = protected, Flashing re = not protected, OFF = no power to unit

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

---

## Dimensions

---

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		

---