



Hospital Grade Short Strap Single Receptacle Back and Side Wire 15A 125V.



Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly. One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire. Terminal compartments isolated from each other for positive conductor containment.
- Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Commercial, Indoor
Application Sector	Hospital Grade	Standard	UL498, cUL/CSA C22.2 No. 42
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	1.018 in
Product Height US	1.68 in		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		
