




adorne Collection  
adorne® 20A Tamper-Resistant Dual-Controlled Outlet, White  
Part No. ARCD202W10



A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Independently cut power to either plug when not in use to conserve energy.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Indoor, Residential, Tamper-Resistant
Application Sector	Residential	Standard	CULUS
Warranty Type	Limited Lifetime Warranty	Type	Outlet

### Dimensions

Product Width US	1.77 in	Product Depth US	1.73 in
Product Height US	2.12 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

## Technical Information

---

Is Tamper-Resistant              Yes                                      Phase                                      Single

---

Connection                          Side and Back Wire                      Number of Wires                      3

---

Number of Gangs                      1    Amperage                                      20 A

---

Number of Poles                      Double Pole                                      Wire Size                                      14 - 10 AWG

---

Indoor/Outdoor                      Indoor    NEMA Configuration Code              5-20R

---

Mounting Type                          Box    Voltage                                      125.0 V

---

Connection Type                      Internal Pressure Plates                      Environmental Conditions              95% (relative humidity, non-condensing)

---